


tML[®] - vertical Patch Cord Managment 90° angled without rings, stainless steel



tML[®] 24

tML[®] 24 is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site – especially in data centres, but also in industrial environments – within the shortest possible time. Heart of the system are the rear MPO/MTP[®] 24 fiber and Telco connectors, which can be used to connect at least six or twelve ports at a time. Depending on the module configuration, transfer rates of up to 400G are currently possible with SR4. The fibre optic and TP modules can be used together in a module carrier with a very high port density. The tde offers its tML[®] cabling system as a proven tML[®] standard system and in the highly innovative variants tML[®]Xtended and now tML[®] 32 for extreme scalability and very easy migration to higher transmission rates such as 40G, 100G, 200G and 400G.



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

tML® - vertical Patch Cord Managment 90° angled without rings, stainless steel

Technical Data

| | |
|------------|------------------------------------------------------------------------------|
| Color | stainless steel (V2A-AiSi 430) |
| Thickness | 1.0 mm |
| Assembly | up to 2 rings |
| Dimensions | 1U, side length outside (incl. mounting): 6.8 cm/ side length behind: 5.0 cm |
| Mounting | on the 19" rail. |
| | QS-Managementsystem ISO 9001, ISO 14001 and TL 9000 |

Product variants & accessories

| Art.-No. | Description |
|------------------|--------------------------------------------------------------------------------|
| TML-RP-BGL-100-K | tML® - FO Patch Cord Management ring plastic, 100mm, black |
| TML-RP-BGL-110 | tML® - TP Patch Cord Managment ring metal, 110mm |
| TML-RP-BGL-56-K | tML® - FO Patch Cord Management ring plastic, 56mm, black |
| TML-RP-VERT | tML® - vertical Patch Cord Managment 90° angled without rings, stainless steel |