

tBL<sup>®</sup> - Wall mount enclosure 300x300x85mm lockable, sidewalls fixed



## tBL<sup>®</sup> - tde Basic Link (FO Enclosures)

The FO enclosures of the tBL<sup>®</sup> - tde Basic Link series are optimized products with a high functionality and an easy handling at the installation. The program includes splice and breakout boxes for 19 inch, wall and DIN rail mounting. These products are characterized by a high port density and an optimal fiber management, so that the permissible bending radii can't be undercut. Moreover, there are no sharp corners or edges, to avoid damage to the pigtails and buffer tubes. The front plates are removable. There are versions for E2000, FC, PC, LC, MPO / MTP, MTRJ, MU, SC, and ST. These products can be obtained with or without equipment. In addition, there are also special versions with IP66 for outdoor and offshore applications.

The compact housing can be used as splice distributor of the fiber optic trunk cable or used as an office distribution.



**tde<sup>®</sup>** trans data elektronik GmbH

### Headquarter address:

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

### Sales office address:

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 8805 61 13  
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

tBL® - Wall mount enclosure 300x300x85mm lockable, sidewalls fixed

## Technical Data

Material	Steel sheet 1.5 mm
Color	7035
Dimensions	300 x 300 x 85 mm (H x W x D)
Pre-mounted	1x small housing
	2x side panel fixed, sheet steel 1 mm, RAL 7035
	1x door lockable, sheet steel 1 mm, RAL 7035
	1x cassettes splice holder quadruple
	1x set wall mounting material
Norms	DIN 50173
Protection class	IP 20
	QS-Managementsystem ISO 9001, ISO 14001 and TL 9000

## Product variants & accessories

Art.-No.	Description
CERN-W300x300x85F	tBL® - Wall mount enclosure 300x300x85mm lockable, sidewalls fixed