

tML[®] - FO partial front plate 5HP with 6x MPO Type A (Key Up/Down) OM4 magenta for the Rack Mount Enclosure 3U black



tML[®] 24

tML[®] 24 is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site – especially in data centres, but also in industrial environments – within the shortest possible time. Heart of the system are the rear MPO/MTP[®] 24 fiber and Telco connectors, which can be used to connect at least six or twelve ports at a time. Depending on the module configuration, transfer rates of up to 400G are currently possible with SR4. The fibre optic and TP modules can be used together in a module carrier with a very high port density. The tde offers its tML[®] cabling system as a proven tML[®] standard system and in the highly innovative variants tML[®]Xtended and now tML[®] 32 for extreme scalability and very easy migration to higher transmission rates such as 40G, 100G, 200G and 400G.

The tML[®] - FO partial front panel MPO/MTP[®] is intended for the installation in the tML[®] Rack Mount Enclosure 3U.



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

tML® - FO partial front plate 5HP with 6x MPO Type A (Key Up/Down) OM4 magenta for the Rack Mount Enclosure 3U black

Technical Data

| | |
|-------------|---|
| Pre-mounted | 6 x MPO/MTP®Adapter (magenta) |
| | QS-Managementsystem ISO 9001, ISO 14001 and TL 9000 |

tML® - partial front panels 5HP

| | |
|-------------|-------|
| Front Panel | Black |
|-------------|-------|

FO Adapters

| | |
|-----------------|--------------------------|
| Type | MPO/MTP® |
| Application | Multimode OM4 |
| Design | without Flange |
| Connector style | SC Simplex |
| Key Orientation | Type A, Key up/down |
| Color | Magenta |
| Material | Plastic |
| Sleeve | -- |
| Shutter | -- |
| Standards | IEC 61754-7 TIA 604-5 |
| Manufacturer | US Conec |

Product variants & accessories

| Art.-No. | Description |
|---------------|--|
| TML-T06MP-GNS | tML® - FO partial front plate 5HP with 6x Type A (Key Up/Down) OS2 green for the Rack Mount Enclosure 3U black |
| TML-T06MP-GRS | tML® - FO partial front plate 5HP with 6x MPO Type B (Key Up/Up) for the Rack Mount Enclosure 3U black |
| TML-T06MP-TKS | tML® - FO partial front plate 5HP with 6x MPO Type A (Key Up/Down) OM3 aqua for the Rack Mount Enclosure 3U black |
| TML-T06MP-VIS | tML® - FO partial front plate 5HP with 6x MPO Type A (Key Up/Down) OM4 magenta for the Rack Mount Enclosure 3U black |