

tBG2 - Module Blind Plate 7HP for subrack 19"/4U



tBG II - tde Subrack

The newest generation of tde - Subracks is developed especially for the application by loose tube cables with high fiber counts. Up to 288 fibers can be distributed to 12 splice modules. Alternative up to 12 tML[®] modules. By the application deep-adjustable 84HP Subrack with 7HP-grid is a simple module mounting possible. The modules are fixed by screws. Cable over lengths are accommodated certainly in a cable tray. The cable tray is removable. The cable entry is on the left and right back side. On the front side is a patch cord management panel with 5 rings integrated.

tBG II - tde subrack 19"/4U is for the equip of up to 12 x tBG II - splice modules 3U/7HP with high component density.

The Module Blind Plate is intended for the cover of unused slots in the subrack 19"/4U (for 12 x Modules).



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

tBG2 - Module Blind Plate 7HP for subrack 19"/4U

Technical Data

Material	stainless steel
Mounting	at the front of the subrack
	QS-Managementsystem ISO 9001, ISO 14001 and TL 9000

Product variants & accessories

Art.-No.	Description
TBG2-T-BLIND	tBG2 - Module Blind Plate 7HP for subrack 19"/4U