

LWL-Nummernschlüssel für Patch- und Trunkkabel

Beispielnummer: L-LC/MP50B12G4-00200

L- S S S S / S S S S F F K K K K K K B X X X X X

Stecker 1/ 2:

BN	Mini BNC
DI	DIN
DIA	DIN APC
E2	E2000
E2A	E2000 APC
E2AC	E2000 APC Compact
E2AP	E2000 APC Premium (0.1 dB)
E2C	E2000 Compact
E2U	E2000 UPC
E2UC	E2000 Compact UPC
ES	Escon (Duplex)
FC	FC
FCA	FC APC
FCU	FC UPC
FS	FSMA
HM	2 bzw. 4 Kanal Plug, HEBM
HMF	2 bzw. 4 Kanal, HEBM Flange Nut Bulkhead
HMJ	2 bzw. 4 Kanal, HEBM Jam Nut Bulkhead
HS	4 Kanal Plug, HEBS
HSJ	4 Kanal, HEBS Jam Nut Bulkhead
HSX	4 Kanal XLR, HEBS
HXL	2 Kanal Plug, HEBXL
HXLf	2 bzw. 12 Kanal, HEBXL Flange Nut Bulkhead
HXLJ	2 bzw. 12 Kanal, HEBXL Jam Nut Bulkhead
LC	LC
LCA	LC APC
LCU	LC UPC
LCJ	LC ODVA Buchse (Duplex)
LCP	LC ODVA Stecker (Duplex)
MI	FDDI (Duplex)
M2	MPO24 Female
M2P	MPO24 Male
MP	MPO12 Female
MPP	MPO12 Male
MT	MT-RJ Female
MT-P	MT-RJ Male
MU	MU
MUU	MU UPC
SC	SC
SCA	SC APC
SCR	SC RJ
SCU	SC UPC
SLC	LC Secure (Duplex)
ST	ST
TLC	LC HD

Fasertyp:

09 9/125µ
50 50/125µ
62 62.5µ125µ

MPO/MTP®

Belegung:

A Typ A
B Typ B
C Typ C

Länge

in cm:

00050 0.5 m
00100 1.0 m
... ..

Kabeltyp:

D	Duplex
D3-	Duplex OM3
D4-	Duplex OM4
D-M	Duplex MiniZip
D3M	Duplex MiniZip OM3
D4M	Duplex MiniZip OM4
S	Simplex
S3-	Simplex OM3
S4-	Simplex OM4
S-M	Simplex MiniZip
S3M	Simplex MiniZip OM3
S4M	Simplex MiniZip OM4
TD	FlatTwin
TD3-	FlatTwin OM3
TD4-	FlatTwin OM4
I12E	Rundkabel SM (12)
I12G	Rundkabel MM OM2 (12)
I12G3-	Rundkabel MM OM3 (12)
I12G4-	Rundkabel MM OM4 (12)
I24G3-	Rundkabel MM OM3 (24)
I24G4-	Rundkabel MM OM4 (24)
B_E	Universalkabel SM (04 - 144)
B_G	Universalkabel MM OM2 (04 - 144)
B_G3-	Universalkabel MM OM3 (04 - 144)
B_G4-	Universalkabel MM OM4 (04 - 144)
P_E	Mil-Tac Breakoutkabel SM (02 - 04)
P_G	Mil-Tac Breakoutkabel MM (02 - 04)
V_E	Breakoutkabel SM (04 - 24)
V_G	Breakoutkabel MM (04 - 24)
V_G3-	Breakoutkabel MM (04 - 24)
V_G4-	Breakoutkabel MM (04 - 24)

* Anzahl der Fasern gemäß Kabeltypbeschreibung auswählen