

tSML - TP Module 19"/0.5U straight 24x RJ45/4x Telco Gigabit Ethernet shielded



tSML - tde Semi Modular Link

tSML is a modular developed cabling system, which consists of two core components: module and trunk cable. The system components, preterminated with connectors and tested ex works, facilitate very fast installation of both twisted pair and fiber-optic cables. Ready-made trunk cables, providing a high number of pairs or fibers, can simply be plugged together using patch panels. Up to 96x LC duplex and/or 48 x RJ45 of haven can be accommodated in such a way on 1U. At the heart of the System are MPO/MTP[®] and Telco connectors, with which 12 optical fibers or 24 copper pairs can be connected simultaneously. Fiber-optic and twisted pair modules can be combined on 1U within a panel without difficulty.

The tSML – Panel 19" 1/2U is not modular developed. This is a space-saving and economical alternative to the modular developed Rack Mount Enclosure 19"/1U. Is by the four back Telco connectors nevertheless a fast Plug& Play installation ensures.



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

tSML - TP Module 19"/0.5U straight 24x RJ45/4x Telco Gigabit Ethernet shielded

Technical Data

Entry	4 x Telco Male shielded GbE
Exit	24 x RJ45 Jacks shielded GbE
Tests	Link Performance Tests, electronic test on allocation and short circuit and final visual inspection
	QS-Managementsystem nach ISO 9001, ISO 14001 und TL 9000

Box	stainless steel
Front plate	stainless steel
Dimensions	19", 0.5U, depth 11 cm

Product variants & accessories

Art.-No.	Description
TSML-M24RJ45/TELCO-M	tSML - TP Module 19"/0.5U straight 24x RJ45/4x Telco Gigabit Ethernet shielded
TSML-TELCO-FF-Cxx	tSML - TP Trunk Cable Telco F/F 180° shielded 1000BaseT LSHF-F, length: xx in m
TSML-TELCO-FF-xx	tSML - TP Trunk Cable Telco F/F 180° shielded 1000BaseT PUR, length: xx in m