

tSML - module 19"/0.5U straight blank without cover f. 4x FO partial front panels or 4x RJ45 DC 6fold



## tSML - tde Semi Modular Link

tSML is a modular developed cabling system, which consists of two core components: module and trunk cable. The system components, preterminated with connectors and tested ex works, facilitate very fast installation of both twisted pair and fiber-optic cables. Ready-made trunk cables, providing a high number of pairs or fibers, can simply be plugged together using patch panels. Up to 96x LC duplex and/or 48 x RJ45 of haven can be accommodated in such a way on 1U. At the heart of the System are MPO/MTP<sup>®</sup> and Telco connectors, with which 12 optical fibers or 24 copper pairs can be connected simultaneously. Fiber-optic and twisted pair modules can be combined on 1U within a panel without difficulty.



**tde<sup>®</sup>** trans data elektronik GmbH

**Headquarter address:**

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

**Sales office address:**

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 8805 61 13  
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

tSML - module 19"/0.5U straight blank without cover f. 4x FO partial front panels or 4x RJ45 DC 6fold

## Technical Data

Box	stainless steel
Front plate	stainless steel
Mounting	Snap-In (4x FO partial front panels or 4x RJ45 DC 6fold)
Cable strain relief	Breakout cable entries, by cable ties
Dimensions	19", 0.5U, depth 11 cm
Identification	silk screen at the front
	19" mounting set enclosed
	QS-Managementsystem ISO 9001, ISO 14001 and TL 9000

## Product variants & accessories

Art.-No.	Description
TSML-M-19/0.5HE-CO	tSML - Cover for Module 19"/0.5U straight
TSML-M-19/0.5HE-KB	tSML - module 19"/0.5U straight blank without cover f. 4x FO partial front panels or 4x RJ45 DC 6fold
TSML-M-BLIND	tSML - blind plate Snap-In for module 19"/0.5U