

tML<sup>®</sup> - partial front plate with 6x MPO/MTP<sup>®</sup> Type A (Key Up/Down) OM4 magenta for the Rack Mount Enclosure 1U



## tML<sup>®</sup> 24

tML<sup>®</sup> 24 is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site – especially in data centres, but also in industrial environments – within the shortest possible time. Heart of the system are the rear MPO/MTP<sup>®</sup> 24 fiber and Telco connectors, which can be used to connect at least six or twelve ports at a time. Depending on the module configuration, transfer rates of up to 400G are currently possible with SR4. The fibre optic and TP modules can be used together in a module carrier with a very high port density. The tde offers its tML<sup>®</sup> cabling system as a proven tML<sup>®</sup> standard system and in the highly innovative variants tML<sup>®</sup>Xtended and now tML<sup>®</sup> 32 for extreme scalability and very easy migration to higher transmission rates such as 40G, 100G, 200G and 400G.

The tML<sup>®</sup> - FO partial front panel MPO/MTP<sup>®</sup> is intended for the installation in the tML<sup>®</sup> Rack Mount Enclosure 1U (for 8 x Modules).



**tde<sup>®</sup> trans data elektronik GmbH**

**Headquarter address:**

Lingener Str. 2  
D-49626 Buppen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

**Sales office address:**

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 8805 61 13  
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

tML® - partial front plate with 6x MPO/MTP® Type A (Key Up/Down) OM4 magenta for the Rack Mount Enclosure 1U

## Technical Data

Pre-mounted	6 x MPO/MTP® Adapter (magenta)
	QS-Managementsystem ISO 9001, ISO 14001 and TL 9000

## tML® Standard - FO Modules MPO/MTP®

Front Panel	Stainless steel
Dimensions	108 x 20 mm

## FO Adapters

Type	MPO/MTP®
Application	Multimode OM4
Design	without Flange
Connector style	SC Simplex
Key Orientation	Type A, Key up/down
Color	Magenta
Material	Plastic
Sleeve	--
Shutter	--
Standards	IEC 61754-7 TIA 604-5
Manufacturer	US Conec

## Product variants & accessories

Art.-No.	Description
TML-M06MP-GN	tML® - partial front plate with 6x MPO/MTP® Type A (Key Up/Down) OS2 green for the Rack Mount Enclosure 1U
TML-M06MP-GR	tML® - partial front plate with 6x MPO/MTP® Type B (Key Up/Up) for the Rack Mount Enclosure 1U
TML-M06MP-LG	tML® - partial front plate with 6x MPO/MTP® Type A (Key Up/Down) OM5 limegreen for the Rack Mount Enclosure 1U
TML-M06MP-TK	tML® - partial front plate with 6x MPO/MTP® Type A (Key Up/Down) OM3 aqua for the Rack Mount Enclosure 1U
TML-M06MP-VI	tML® - partial front plate with 6x MPO/MTP® Type A (Key Up/Down) OM4 magenta for the Rack Mount Enclosure 1U