

tBL[®] - Breakout Panel 19"/0.5U angled blank w/o cover for 4x RJ45 DC 6fold 10GbE



tBL[®] - tde Basic Link (TP)

tBL[®] tde Basic Link (TP) is a complete system solution for structured cabling in Cat6A for transfer rates of up to 10GbE in real time. The tBL[®] - cabling link corresponds to a permanent link in accordance with ISO / IEC 11801 (EN 50173). The RJ45 modules are available in the form factors Keystone (KS) and Data Center (DC). The compact design of the 6fold RJ45 DC module allows a high packing density of up to 48 RJ45 ports on 1U. The RJ45 module is connected to the tBL[®] - cable termination block by simply plugging. The slim cable termination block can be easily assembled on the cable by using the tBL[®] - crimp tool and is suitable for preterminated cables. The modular design of individual RJ45 modules are interchangeable at any time without termination. A cost effective alternative product is the RJ45 keystone module without cable termination block in the tool-less design.

The system solution is complemented by an extensive portfolio of carrier systems. These include design-capable data outlets, floor box frames, Consolidation points, DIN rail modules and patch panels in 1/2 and 1U.

For equipping up to four tBL[®] - RJ45 DC 6er Modules.



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

tBL[®] - Breakout Panel 19"/0.5U angled blank w/o cover for 4x RJ45 DC 6fold 10GbE

Technical Data

Box	stainless steel
Front plate	stainless steel
Mounting	Snap-In (4x RJ45 DC 6er Modules 10GbE)
Cable strain relief	Breakout cable entries, by cable ties
Dimensions	19", 0.5 U, depth: 10.5 cm (outside) / 20.5 cm (centered)
Identification	silk screen at the front
	19" mounting set enclosed
	QS-Managementsystem ISO 9001, ISO 14001 and TL 9000

Product variants & accessories

Art.-No.	Description
TBL-M-BLIND	tBL [®] - blind plate Snap-In for Breakout Panel 19"/0.5U
TBL-MS-19/0.5HE-KB	tBL [®] - Breakout Panel 19"/0.5U angled blank w/o cover for 4x RJ45 DC 6fold 10GbE
TBL-MS-COVER	tBL [®] - Cover for Breakout Panel 19"/0.5U angled