

Finisar - SFP+ 16G Transceiver, Multimode LC, 14.025 Gb/s, 35m/100m

Technical Data

Key Features	Up to 14.025 Gb/s bi-directional data links
	Hot-pluggable SFP+ footprint
	Built-in digital diagnostic functions
	Built-in CDR with shut off control
	850 nm Oxide VCSEL laser transmitter
	Duplex LC connector
	RoHS compliant and Lead-Free
	35m on 50/125µm MMF
	100m on high-bandwidth 50/125µm (OM3) MMF
	Metal enclosure, for lower EMI
	Single 3.3 V power supply
	Extended operating temperature range: 0°C to +70°C

Applications	Tri-Rate 4.25/8.5/14.025 Gb/s Fiber Channel
--------------	---

On request also available for	Brocade - XBR-000192
-------------------------------	----------------------

Weblink	http://www.finisar.com/products/optical-transceivers/sfp-plus/FTLF8529P3BCV
---------	---

Product variants & accessories

Art.-No.	Description
FTLF1429P3BCV	Finisar - SFP+ 16G Transceiver, Singlemode LC, 14.025 Gb/s, 10km
FTLF8529P4BCV	Finisar - SFP+ 16G Transceiver, Multimode LC, 14.025 Gb/s, 35m/100m