

tBL<sup>®</sup> - Consolidationpoint-Housing for 3U/8HP, without front panel, black



## tBL<sup>®</sup> - tde Basic Link (TP)

tBL<sup>®</sup> tde Basic Link (TP) is a complete system solution for structured cabling in Cat6A for transfer rates of up to 10GbE in real time. The tBL<sup>®</sup> - cabling link corresponds to a permanent link in accordance with ISO / IEC 11801 (EN 50173). The RJ45 modules are available in the form factors Keystone (KS) and Data Center (DC). The compact design of the 6fold RJ45 DC module allows a high packing density of up to 48 RJ45 ports on 1U. The RJ45 module is connected to the tBL<sup>®</sup> - cable termination block by simply plugging. The slim cable termination block can be easily assembled on the cable by using the tBL<sup>®</sup> - crimp tool and is suitable for preterminated cables. The modular design of individual RJ45 modules are interchangeable at any time without termination. The RJ45 modules are optional with a LID - Light ID function available. This feature facilitates searching of related ports within a cable link. A cost effective alternative product is the RJ45 keystone module without cable termination block in the tool-less design.

The system solution is complemented by an extensive portfolio of carrier systems. These include design-capable data outlets, floor box frames, Consolidation points, DIN rail modules and patch panels in 1/2 and 1U.

- Elegant housing for wall-, ceiling- and floormounting



**tde<sup>®</sup> trans data elektronik GmbH**

**Headquarter address:**

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

**Sales office address:**

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 914 36 99  
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

## tBL<sup>®</sup> - Consolidationpoint-Housing for 3U/8HP, without front panel, black

- Inclusion (optional) current for all splice cassettes
- FO- and copper applications
- Front panels for all 10" / 19" (depending on housingtyp)
- Usable with standard partial panels 3U/8HP
- tML<sup>®</sup> compatible
- Construction for various applications
- Cable In- and output (single strain relief) possible

### Technical Data

Housing	For 3U/8HP, consisting of: bottom tray with strain relief on both sides and cover with dust caps and sealing lips
Front panel	No (for inclusion of different 3U/8HP front panels)
Dimensions	50 x 130 x 300 mm (HxWxD)
Material	Steel 1203
Colour	RAL 9005 (black)

### Product variants & accessories

Art.-No.	Description
TBL-CONS10/1HE-GR	tBL <sup>®</sup> - Consolidationpoint-Housing for 10", without front panel, grey
TBL-CONS10/1HE-SW	tBL <sup>®</sup> - Consolidationpoint-Housing for 10", without front panel, black
TBL-CONS19/1HE-GR	tBL <sup>®</sup> - Consolidationpoint-Housing for 19", without front panel, grey
TBL-CONS19/1HE-SW	tBL <sup>®</sup> - Consolidationpoint-Housing for 19", without front panel, black
TBL-CONS3HE/8TE-GR	tBL <sup>®</sup> - Consolidationpoint-Housing for 3U/8HP, without front panel, grey
TBL-CONS3HE/8TE-SW	tBL <sup>®</sup> - Consolidationpoint-Housing for 3U/8HP, without front panel, black