

tBL[®] - Consolidationpoint-Housing for 3U/8HP, without front panel, black



tBL[®] - tde Basic Link (TP)

tBL[®] tde Basic Link (TP) is a complete system solution for structured cabling in Cat6A for transfer rates of up to 10GbE in real time. The tBL[®] - cabling link corresponds to a permanent link in accordance with ISO / IEC 11801 (EN 50173). The RJ45 modules are available in the form factors Keystone (KS) and Data Center (DC). The compact design of the 6fold RJ45 DC module allows a high packing density of up to 48 RJ45 ports on 1U. The RJ45 module is connected to the tBL[®] - cable termination block by simply plugging. The slim cable termination block can be easily assembled on the cable by using the tBL[®] - crimp tool and is suitable for preterminated cables. The modular design of individual RJ45 modules are interchangeable at any time without termination. The RJ45 modules are optional with a LID - Light ID function available. This feature facilitates searching of related ports within a cable link. A cost effective alternative product is the RJ45 keystone module without cable termination block in the tool-less design.

The system solution is complemented by an extensive portfolio of carrier systems. These include design-capable data outlets, floor box frames, Consolidation points, DIN rail modules and patch panels in 1/2 and 1U.

- Elegant housing for wall-, ceiling- and floormounting



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

tBL[®] - Consolidationpoint-Housing for 3U/8HP, without front panel, black

- Inclusion (optional) current for all splice cassettes
- FO- and copper applications
- Front panels for all 10" / 19" (depending on housingtyp)
- Usable with standard partial panels 3U/8HP
- tML[®] compatible
- Construction for various applications
- Cable In- and output (single strain relief) possible

Technical Data

| | |
|-------------|---|
| Housing | For 3U/8HP, consisting of: bottom tray with strain relief on both sides and cover with dust caps and sealing lips |
| Front panel | No (for inclusion of different 3U/8HP front panels) |
| Dimensions | 50 x 130 x 300 mm (HxWxD) |
| Material | Steel 1203 |
| Colour | RAL 9005 (black) |

Product variants & accessories

| Art.-No. | Description |
|--------------------|--|
| TBL-CONS10/1HE-GR | tBL [®] - Consolidationpoint-Housing for 10", without front panel, grey |
| TBL-CONS10/1HE-SW | tBL [®] - Consolidationpoint-Housing for 10", without front panel, black |
| TBL-CONS19/1HE-GR | tBL [®] - Consolidationpoint-Housing for 19", without front panel, grey |
| TBL-CONS19/1HE-SW | tBL [®] - Consolidationpoint-Housing for 19", without front panel, black |
| TBL-CONS3HE/8TE-GR | tBL [®] - Consolidationpoint-Housing for 3U/8HP, without front panel, grey |
| TBL-CONS3HE/8TE-SW | tBL [®] - Consolidationpoint-Housing for 3U/8HP, without front panel, black |