

MEDIA CONVERTER- Hardened Ethernet PoE+ Injector, (2) 10/100/1000Base-TX, 100/1000Base-X SFP



(1) 100/1000Base-X SFP Port

+ (2) 10/100/1000Base-T PoE+ Ports

## Description

The SI-IES-121D-LRT is a (3) port unmanaged hardened PoE+ injector/converter that adds up to 30 Watts of power from its (2) PoE+ ports onto 2 network segments. The gigabit speed SFP port provides the ultimate flexibility by allowing fiber SFP uplink ports with varying communication distances.

## Features

- IEEE 802.3at PoE+ to supply 30 Watts per port
- IEEE 802.3af Compatible
- Supports dual speed for SFP slot
- Non-blocking architecture
- Compact, space saving, size
- IP31 housing protection
- Link Pass Through
- Extended operating temperature (-40°C to 75°C)



**tde<sup>®</sup> trans data elektronik GmbH**

### Hausanschrift:

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

### Vertriebsbüro:

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 914 36 99  
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

## MEDIA CONVERTER- Hardened Ethernet PoE+ Injector, (2) 10/100/1000Base-TX, 100/1000Base-X SFP

- DIN Rail mount / optional wall mount brackets included
- Supports full/half duplex flow control
- Supports Auto-MDI/MDI-X
- Supports auto-negotiation
- Supports store-and-forward transmission
- Supports 10K byte jumbo frames

Show product on manufacturers website: <https://www.transition.com/products/media-converters/si-ies-121d-lrt/>

## Technische Daten

### Specifications

## Artikelvarianten & Zubehör

Art.-Nr.	Beschreibung
SI-IES-121D-LRT	MEDIA CONVERTER- Hardened Ethernet PoE+ Injector, (2) 10/100/1000Base-TX, 100/1000Base-X SFP