

(4) 10/100/1000Base-T +, (4) 100/1000 SFP Ports,



Direct Attach Cables / Active Optical Cables

A simple to install, cost-effective and interoperable solution

Often used for data center short-reach interconnects, Direct Attach, Active Copper and Active Optical Cables are an indispensable part of any network.

Terminated with transceiver-style connectors, they are designed to be used in the same ports as a typical SFP+ or QSFP transceiver, with no need for adapters or converters. Our DAC and AOC cables offer compatibility with a huge range of vendors, enabling the connectivity you need within the Top of Rack and End of Row environments.

- 10G, 25G, 40G & 100G product solutions
- Seamless interoperability with network equipment
- Multi-code options enabling different OEM vendors at each end of the cable
- 4x breakout cables, 40G QSFP+ to 4x 10G SFP and 100G QSFP28 to 4x 25G SFP28
- Fast Delivery, Custom solutions
- Compatible with Over 90 Systems
- Savings of up to 70%



tde® trans data elektronik GmbH

Hausanschrift:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Vertriebsbüro:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

(4) 10/100/1000Base-T +, (4) 100/1000 SFP Ports,

Product Description

The SISGM1040-244-LRT is a (8) port managed Gigabit switch with (4) dual speed SFP ports providing the ultimate flexibility by allowing SFP fiber connections at Fast Ethernet or Gigabit speeds at a variety of communication distances. Maximum network reliability can be achieved by using the ports in a redundant ring configuration.

Features

- Backplane switch fabric: 16 Gbps
- 1 Mbits Packet Buffer
- SFP ports support 100/1000 Dual Mode
- Store-and-Forward Switching Architecture with 8K MAC Address Table
- Extended operating temperature (-40°C to 75°C)
- Dry Contact Relay Alarm Output
- Wide-range Redundant Power Design
- X-Ring and RSTP Redundancy
- SSL/SSH
- DIN Rail Mounting and Wall Mount Brackets
- Barrel connector interface cable for external AC/DC power supply
- Class 1, Div 2 Certified

Show product on manufacturers website: <https://www.lantronix.com/products/>

Technische Daten

Specifications

Artikelvarianten & Zubehör

Art.-Nr.	Beschreibung
SISGM1040-244-LRT	(4) 10/100/1000Base-T +, (4) 100/1000 SFP Ports,