

Unmanaged Hardened Fast Ethernet Switch, (5) 10/100Base-TX Ports or (8) 10/100Base-TX Ports



(8) 10/100Base-TX (RJ-45) [100 m/328 ft.]

## Description

The SISTF1010-2x0-LRT Fast Ethernet switch family contains simple "Plug-and-Play" multi-port switches of either (5) or (8) ports. This switch family is best used at the edge of a hardened network to provide connections for devices in hazardous locations.

## Features

- Auto-Negotiation
- Auto-MDI/MDIX
- Store-and-Forward Switching Architecture with MAC Address Table
- Extended operating temperature (-40°C to 75°C)
- Dry Contact Relay Alarm Output
- Dual, Redundant DC Power Inputs
- DIN Rail Mounting and Wall Mount Brackets Included
- Reverse Polarity Power Input Protection
- Overload Current Protection
- Barrel connector interface cable included for connecting external AC/DC power supply



**tde<sup>®</sup>** trans data elektronik GmbH

### Hausanschrift:

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

### Vertriebsbüro:

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 914 36 99  
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

## Unmanaged Hardened Fast Ethernet Switch, (5) 10/100Base-TX Ports or (8) 10/100Base-TX Ports

- Class 1, Div 2 Certified

Show product on manufacturers website: <https://www.transition.com/products/switch/sistf1010-2x0-lrt/>

## Technische Daten

## Specifications

## Artikelvarianten & Zubehör

Art.-Nr.	Beschreibung
SISTF1010-280-LRT	Unmanaged Hardened Fast Ethernet Switch, (5) 10/100Base-TX Ports or (8) 10/100Base-TX Ports