

Unmanaged Hardened Fast Ethernet Switch, (4) 10/100Base-TX Ports + (1) 100Base-FX Port



Direct Attach Cables / Active Optical Cables

A simple to install, cost-effective and interoperable solution

Often used for data center short-reach interconnects, Direct Attach, Active Copper and Active Optical Cables are an indispensable part of any network.

Terminated with transceiver-style connectors, they are designed to be used in the same ports as a typical SFP+ or QSFP transceiver, with no need for adapters or converters. Our DAC and AOC cables offer compatibility with a huge range of vendors, enabling the connectivity you need within the Top of Rack and End of Row environments.

- 10G, 25G, 40G & 100G product solutions
- Seamless interoperability with network equipment
- Multi-code options enabling different OEM vendors at each end of the cable
- 4x breakout cables, 40G QSFP+ to 4x 10G SFP and 100G QSFP28 to 4x 25G SFP28
- Fast Delivery, Custom solutions
- Compatible with Over 90 Systems
- Savings of up to 70%



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

Unmanaged Hardened Fast Ethernet Switch, (4) 10/100Base-TX Ports + (1) 100Base-FX Port

(4) 10/100Base-TX (RJ-45) [100 m/328 ft.]

+ (1) 100Base-FX 1300nm multimode (ST)

[2 km/1.2 mi.] Link Budget: 11.0 dB

Description

The SISTF101x-241-LRT is a (5) port unmanaged hardened Ethernet switch that can be used at the edge of a hardened network to provide connections for devices in hazardous locations. Depending on the model, these switches can provide multimode or single mode fiber connections with SC or ST connectors for extended distance communications up to 20 kilometers.

Features

- Auto-Negotiation
- Auto-MDI/MDIX
- DIN Rail Mounting and Wall Mount Brackets Included
- Extended operating temperature (-40°C to 75°C)
- Dual Auto-Sensing Redundant DC Power Inputs
- Barrel connector interface cable included for connecting external AC/DC power supply
- Class 1, Div 2 Certified

Show product on manufacturers website: <https://www.lantronix.com/products/>

Technical Data

Specifications

Product variants & accessories

Art.-No.	Description
SISTF1011-241-LRT	Unmanaged Hardened Fast Ethernet Switch, (4) 10/100Base-TX Ports + (1) 100Base-FX Port