


IND MGD SWITCH(16)10/100Base-TX + (2) SFP COMBO PORTS – ATEX



(16) 10/100Base-TX (RJ-45)

[100 m/328 ft.] with (2) 10/100/1000Base-T

(RJ-45) or (2) 100/1000Base-X SFP Combo

ports

Description

The SISTM1040-262D-LRT-B switch is a (18) port managed hardened switch with (2) copper ports or (2) dual speed SFP ports supporting Fast Ethernet to Gigabit Ethernet speeds. The (2) SFP ports provide the ultimate flexibility by allowing SFP fiber connections at different speeds and at a variety of communication distances. The ports can also be used in a redundant ring for maximum network reliability

Features

- Auto-Negotiation
- Auto-MDI/MDIX



tde[®] trans data elektronik GmbH

Hausanschrift:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Vertriebsbüro:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

IND MGD SWITCH(16)10/100Base-TX + (2) SFP COMBO PORTS – ATEX

- Combo SFP ports support 100/1000Base-X SFPs
 - Extended Operating Temperature (-40°C to +70°C)
 - Dry Contact Relay Alarm Output
 - Dual, Redundant, Auto-Sensing 12-48 VDC Power Inputs
 - Overload Current Protection
 - DIN Rail Mounting and Wall Mount Brackets Included
 - PTP- Precision Timing Protocol
 - RMON
 - Port Based VLAN (4096)
 - IEEE 802.1Q Tag VLAN
 - GVRP
 - Port Trunk with LACP QoS (Quality of Service)
 - IEEE 802.1p Class of Service, Per port provides priority queues
 - Port Based, Tag Based and Type of Service Priority
 - SSL V2, V3, TLS V1.0, SSH-V2
 - Port Security: MAC address entries/filter
-
- IP Security: IP address security management to prevent unauthorized intruder
 - Login Security: IEEE 802.1X/RADIUS Authentication IGMP Query mode for Multi-Media Application
 - IGMP Multicast groups 1024
 - Support O-ring and multi-ring, STP, RSTP, MSTP
 - Provide redundant backup feature and recovery time below 20ms.
-
- SNMP v1 v2c, v3/Web/Telnet/CLI
 - DHCP Client/DHCP Server
 - TFTP Firmware Upgrade
 - TFTP Configuration Backup/Restore
 - IPv4/IPv6 dual-stack

Show product on manufacturers website: <https://www.transition.com/products/switch/sistm1040-262d-lrt-b/>

Technische Daten

Specifications

Artikelvarianten & Zubehör

Art.-Nr.	Beschreibung
SISTM1040-262D-LRT-B	IND MGD SWITCH(16)10/100Base-TX + (2) SFP COMBO PORTS – ATEX