

TN-CWDM-SFP-1xx0-16 - Cisco Compatible CWDM SFP Modules, 1000Base-LX/ZX Fiber Channel (LC)

[160 km/99.4 mi.]

Lantronix / Transition Networks

1000Base-LX/ZX Fiber Channel single mode (LC) with DMI 1510nm [160 km/99.4 mi.] Link Budget: 36.0 dB

Product Description

1000Base-LX/ZX Fiber Channel single mode (LC) with DMI [160 km/99.4 mi.] Link Budget: 36.0 dB

Features

- Coarse Wavelength Division Multiplexing (CWDM) ITU Grid Compliant Wavelength
- Hot-Pluggable SFP Optical Transceiver With Duplex LC Connector
- Digital Diagnostic Function (DMI)
- Class 1 Laser International Safety Standard IEC-60825 Compliant
- Compatible with SFP Multi-Sourcing Agreement (MSA)
- Single +3.3V Power Supply
- RoHS Compliant
- Compliant with IEEE 802.3z 1000Base-LX/ZX
- Compliant with Fiber Channel 1x SM-LC-L FC-PI
- Compliant with IEEE 802.3z 1000Base-LX/ZX
- Compliant with Fiber Channel
- 1x SM-LC-L FC-PI

Show product on manufacturers website: <https://www.lantronix.com/products/>



tde[®] trans data elektronik GmbH

Hausanschrift:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Vertriebsbüro:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

TN-CWDM-SFP-1xx0-16 - Cisco Compatible CWDM SFP Modules, 1000Base-LX/ZX Fiber Channel (LC)
[160 km/99.4 mi.]

Technische Daten

Specifications

Artikelvarianten & Zubehör

Art.-Nr.	Beschreibung
TN-CWDM-SFP-1510-16	TN-CWDM-SFP-1xx0-16 - Cisco Compatible CWDM SFP Modules, 1000Base-LX/ZX Fiber Channel (LC) [160 km/99.4 mi.]