

TRANSCEIVER- SFP,CC,100BASE-BX,1310/1550,SM LC,40KM,3.3V,DMI,-40-85C

Direct Attach Cables / Active Optical Cables

A simple to install, cost-effective and interoperable solution

Often used for data center short-reach interconnects, Direct Attach, Active Copper and Active Optical Cables are an indispensable part of any network.

Terminated with transceiver-style connectors, they are designed to be used in the same ports as a typical SFP+ or QSFP transceiver, with no need for adapters or converters. Our DAC and AOC cables offer compatibility with a huge range of vendors, enabling the connectivity you need within the Top of Rack and End of Row environments.

- 10G, 25G, 40G & 100G product solutions
- Seamless interoperability with network equipment
- Multi-code options enabling different OEM vendors at each end of the cable
- 4x breakout cables, 40G QSFP+ to 4x 10G SFP and 100G QSFP28 to 4x 25G SFP28
- Fast Delivery, Custom solutions
- Compatible with Over 90 Systems
- Savings of up to 70%

100Base-BX 1310nm TX/1550nm RX single fiber single mode (Duplex LC) with DMI [40 km/24.9 mi.] Link Budget: 26.0 dB

Product Description

100Base-BX 1310nm TX/1550nm RX single fiber single mode (Duplex LC)
with DMI [40 km/24.9 mi.] Link Budget: 26.0 dB

Features

- Hot-Pluggable SFP Footprint Duplex LC Optical Transceiver
- Class 1 Laser International Safety Standard IEC-60825 Compliant
- Compatible with SFP Multi-Sourcing Agreement (MSA)
- Compliant with IEEE 802.3 100Base-FX
- Compliant with IEEE 802.3ah 100Base-FX
- Compliant with Intermediate-Reach SONET OC-3/SDH STM-1 (S-1.1)
- Can be used on Optical Line Converter xFMFF4040-100

Show product on manufacturers website: <https://www.lantronix.com/products/>



tde[®] trans data elektronik GmbH

Hausanschrift:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Vertriebsbüro:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

TRANSCEIVER- SFP,CC,100BASE-BX,1310/1550,SM LC,40KM,3.3V,DMI,-40-85C

Technische Daten

Specifications

Artikelvarianten & Zubehör

Art.-Nr.	Beschreibung
TN-GLC-FE-U-40-RGD	TRANSCEIVER- SFP,CC,100BASE-BX,1310/1550,SM LC,40KM,3.3V,DMI,-40-85C