

TRANSCEIVER- SFP, CWDM, 1310NM, 1000BASE-LX, SM LC,160KM, 3.3V,DMI

Lantronix / Transition Networks

1000Base-LX/Fiber Channel 1x single mode (LC) with DMI 1310nm [160 km/99.4 mi.] Link Budget: 37.0 dB

Product Description

1000Base-LX/Fiber Channel 1x single mode (LC) with DMI [160 km/99.4 mi.] Link Budget: 37.0 dB

Features

- Coarse Wavelength Division Multiplexing (CWDM) ITU Grid Compliant Wavelengths
- Hot-Pluggable SFP Footprint Duplex LC Optical Transceiver
- Digital Diagnostic Function (DMI)
- Class 1 Laser International Safety Standard IEC-60825 Compliant
- Compatible with SFP Multi-Sourcing Agreement (MSA)
- Compliant with Fiber Channel 1X SM-LC-L FC-PI (Can be used on Optical Line Converter xFMFF4040-100)

Show product on manufacturers website: <https://www.lantronix.com/products/>



tde[®] trans data elektronik GmbH

Hausanschrift:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Vertriebsbüro:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

TRANSCEIVER- SFP, CWDM, 1310NM, 1000BASE-LX, SM LC,160KM, 3.3V,DMI

Technische Daten

Specifications

Artikelvarianten & Zubehör

Art.-Nr.	Beschreibung
TN-SFP-LX16-C31	TRANSCEIVER- SFP, CWDM, 1310NM, 1000BASE-LX, SM LC,160KM, 3.3V,DMI