

100Base-FX/OC-3 1310nm multimode (LC) with DMI [2 km/1.2 mi.] Link Budget: 11.0 dB; UL Listed



Direct Attach Cables / Active Optical Cables

A simple to install, cost-effective and interoperable solution

Often used for data center short-reach interconnects, Direct Attach, Active Copper and Active Optical Cables are an indispensable part of any network.

Terminated with transceiver-style connectors, they are designed to be used in the same ports as a typical SFP+ or QSFP transceiver, with no need for adapters or converters. Our DAC and AOC cables offer compatibility with a huge range of vendors, enabling the connectivity you need within the Top of Rack and End of Row environments.

- 10G, 25G, 40G & 100G product solutions
- Seamless interoperability with network equipment
- Multi-code options enabling different OEM vendors at each end of the cable
- 4x breakout cables, 40G QSFP+ to 4x 10G SFP and 100G QSFP28 to 4x 25G SFP28
- Fast Delivery, Custom solutions
- Compatible with Over 90 Systems
- Savings of up to 70%



tde® trans data elektronik GmbH

Hausanschrift:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Vertriebsbüro:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

100Base-FX/OC-3 1310nm multimode (LC) with DMI [2 km/1.2 mi.] Link Budget: 11.0 dB; UL Listed

Applications include: Fast Ethernet / OC3 Switches and Routers, xDSL Applications, and Metro Edge Switching.

Features

- Hot-Pluggable SFP Footprint Optical Transceiver
- Digital Diagnostic Function
- Compliant with SFP Multi-Sourcing Agreement (MSA)

Technische Daten

Standards

- IEEE 802.3

Dimensions

- Width: 0.52" [13 mm]
- Depth: 2.18" [55 mm]
- Height: 0.33" [8 mm]

Power Consumption

- 0.66 Watts

Power Input

- 3.3V

Environment

- Operating: 0°C to 70°C
- Operating: -40°C to 85°C (TN-SFP-OC3MT)

Certifications

- IEC-60825, FDA 21, CFR 1040.10 and 1040.11; UL Listed (specific SKUs only)

Warranty

100Base-FX/OC-3 1310nm multimode (LC) with DMI [2 km/1.2 mi.] Link Budget: 11.0 dB; UL Listed

- Lifetime

Artikelvarianten & Zubehör

Art.-Nr.	Beschreibung
TN-SFP-OC3M	100Base-FX/OC-3 1310nm multimode (LC) with DMI [2 km/1.2 mi.] Link Budget: 11.0 dB; UL Listed