

TRANSCEIVER- SFP,1000BASE-SX,1310TX/1550RX, MM LC,500M,3.3V

1000Base-SX 1310nm TX/1550nm RX multimode (Simplex LC) with DMI [500 m/1640 ft.] Link Budget: 7.0 dB

Product Description

1000Base-SX 1310nm TX/1550nm RX multimode (Simplex LC) with DMI [500 m/1640 ft.] Link Budget: 7.0 dB

Features

- Hot-Pluggable SFP Footprint Optical Transceiver
- Digital Diagnostic Function
- Class 1 Laser International Safety Standard IEC-60825 Compliant
- Compatible with SFP Multi-Sourcing Agreement (MSA)

Show product on manufacturers website: <https://www.transition.com/products/optical-devices/tn-sfp-sxb1/>



tde[®] trans data elektronik GmbH

Hausanschrift:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Vertriebsbüro:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

TRANSCEIVER- SFP,1000BASE-SX,1310TX/1550RX, MM LC,500M,3.3V

Technische Daten

Specifications

Artikelvarianten & Zubehör

Art.-Nr.	Beschreibung
TN-SFP-SXB1	TRANSCEIVER- SFP,1000BASE-SX,1310TX/1550RX, MM LC,500M,3.3V