

TRANSCEIVER- XFP,10GBASE-LR, CWDM, 10G, SM LC,1530nm,70KM, 3.3V,DMI

Lantronix / Transition Networks

XFP 10GBase-ZR single mode (LC) with DMI 1530nm [70 km/43.6 mi.] Link Budget: 23.0 dB

Product Description

XFP 10GBase-ZR single mode (LC) with DMI [70 km/43.6 mi.] Link Budget: 23.0 dB

Features

- Coarse Wavelength Division Multiplexing (CWDM) ITU Grid Compliant Wavelengths
- Hot-Pluggable SFP Footprint Duplex LC Optical Transceiver
- Digital Diagnostic Function (DMI)
- Class 1 Laser International Safety Standard IEC-60825 Compliant
- Compatible with SFP Multi-Sourcing Agreement (MSA)

Show product on manufacturers website: <https://www.lantronix.com/products/>



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

TRANSCEIVER- XFP,10GBASE-LR, CWDM, 10G, SM LC,1530nm,70KM, 3.3V,DMI

Technical Data

Specifications

Product variants & accessories

Art.-No.	Description
TN-XFP-LR7-C53	TRANSCEIVER- XFP,10GBASE-LR, CWDM, 10G, SM LC,1530nm,70KM, 3.3V,DMI