

PCI Fast Ethernet Fiber Network Interface Cards, 100Base-FX



100Base-FX 1300nm multimode (MT-RJ)

[2 km/1.2 mi.] Link Budget: 14.5 dB

Description

The PCI Fast Ethernet NIC provides a 100Base-FX fiber port and delivers low cost, fiber optic connectivity to the desktop in fiber rich LAN environments. With both standard and low profile form factors, driver support for common operating systems and PCI 2.2 plug-and-play capabilities, installation is a breeze in virtually any PC in your network.

Features

- PCI 32-bit bus master
- Supports 802.1P/Q VLAN tags
- IP multicast filter
- PCI 2.1 and 2.2 compliant
- Wake-on-LAN (WoL) power management supported via the PCI Bus or through the supplied WoL cable
- Standard bracket attached, low-profile bracket included



tde[®] trans data elektronik GmbH

Hausanschrift:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Vertriebsbüro:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

PCI Fast Ethernet Fiber Network Interface Cards, 100Base-FX

- PXE Remote boot support
- Supports ACPI

Show product on manufacturers website: <https://www.transition.com/products/network-adapters/n-fx-xx-03/>

Technische Daten

Specifications

Artikelvarianten & Zubehör

Art.-Nr.	Beschreibung
N-FX-MT-03	PCI Fast Ethernet Fiber Network Interface Cards, 100Base-FX