

PCMCIA Fast Ethernet Fiber Network Interface Cards, 100Base-FX



100Base-FX 1300nm multimode (SC)

[2 km/1.2 mi.] Link Budget: 12.0 dB

Description

Fast Ethernet PCMCIA cards provide a 100Base-FX fiber port to deliver fiber optic connectivity to the laptop in high-security, fiber rich LAN environments. Offered in a high-performance 32-bit CardBus version for laptop PCs, the PCM32-FX-xx-01 Series helps save money by eliminating the need for a docking station and a fixed, fiber NIC.

Features

- Complies with PCMCIA standard
- Complies with the IEEE 802.3u 100Base-FX standards
- Fiber connectivity to a legacy laptop supporting the PCMCIA standard
- Single LED to provide link and activity status
- Multimode SC, LC or ST connectors
- Meets Class I Laser safety requirements
- Driver support for wide variety of operating systems



tde[®] trans data elektronik GmbH

Hausanschrift:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Vertriebsbüro:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

PCMCIA Fast Ethernet Fiber Network Interface Cards, 100Base-FX

Show product on manufacturers website: <https://www.transition.com/products/network-adapters/pcm32-fx-xx-01/>

Technische Daten

Specifications

Artikelvarianten & Zubehör

Art.-Nr.	Beschreibung
PCM32-FX-SC-01	PCMCIA Fast Ethernet Fiber Network Interface Cards, 100Base-FX