

Mini 10/100/1000BT -1000BX Switch, SC MM, 3.3V- W/BR

10/100/1000Base-T (RJ-45) [100 m/328 ft.]

to 1000Base-SX 850nm multimode (SC)

[62.5/125 µm fiber: 220 m/722 ft.]

Link Budget: 7.0 dB [50/125 µm fiber: 550

m/1804 ft.] Link Budget: 7.0 dB

Description

The M/GE-PSW Series is a Gigabit Ethernet stand-alone Mini media converter that provides cost effective, entry-level media conversion between 10/100/1000Base-T ports and 1000Base-SX/LX ports. With its fixed configuration, deployments are just plug-and-play, and with its small size, it is ideal for locations where space is limited. Operating at Layer 2, the data link layer, this converter not only converts copper to fiber, it also provides rate conversion allowing legacy 10/100 copper devices to connect to 1000Base-SX/LX fiber.

Features

- Unit & Port LEDs allow for quick status information
- Auto-Negotiation
- Fixed Full-Duplex on fiber
- Auto-MDI/MDIX
- Fixed Link Pass Through
- Automatic Link Restoration
- Space saving design
- Connect Legacy Networking Equipment: Connect an existing 10/100 Mbps device to 1000 Mbps devices.

Show product on manufacturers website: <https://www.transition.com/products/media-converters/mge-psw-xx-01-series/>



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

Mini 10/100/1000BT -1000BX Switch, SC MM, 3.3V- W/BR

Product variants & accessories

Art.-No.	Description
M/GE-PSW-SX-01-BR	Mini 10/100/1000BT -1000BX Switch, SC MM, 3.3V- W/BR