

DS3-T3/ES COAX TO FIBER, MM SC, 2KM W/EU

Lantronix / Transition Networks

(2) Coax (BNC) to 1300nm multimode (SC)

[2 km/ 1.2 mi.] Link Budget: 11.0 dB

Description

The ION S6210 is a managed stand-alone media converter that provides a solution for those users that need to extend DS3-T3/E3 connections over fiber. The S6210 is available in versions that support fixed fiber connectors as well as SFP fiber modules offering support for a variety of fiber types, distances, and wavelengths to provide maximum flexibility across a variety of network topologies. CWDM SFPs can also be utilized to further increase the bandwidth capacity of the fiber infrastructure.

The S6210 DS3-T3/E3 converters must be used in pairs. Management of the stand-alone converter is supported, in-band, over the fiber, when the remote S6210 is linked to a C6210 card installed in a managed ION chassis.

Features

- AIS (Alarm Indication Signal)
- Coax Line Build Out
- Switch selectable for DS3/T3 or E3
- Remote firmware upgrade
- Loopback à Coax and Fiber
- LEDs for immediate visual status
- Supports dual or single fiber
- Supports multimode and single mode fiber at a variety of distances
- Supports CWDM SFPs
- SNMP management when used with ION chassis and management module
- Remote stand-alone can be managed by local peer

Show product on manufacturers website: <https://www.lantronix.com/products/>



tde[®] trans data elektronik GmbH

Hausanschrift:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Vertriebsbüro:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

DS3-T3/ES COAX TO FIBER, MM SC, 2KM W/EU

Artikelvarianten & Zubehör

Art.-Nr.	Beschreibung
S6210-3013-EU	DS3-T3/ES COAX TO FIBER, MM SC, 2KM W/EU