

10Gbase-ZR/1000Base-ZX, SFP+ with DMI 1530nm single mode (LC) [80km/49.7 mi.] Link Budget:
22.0 dB



Lantronix / Transition Networks

Features

- SFP+ Optical Transceiver
- 10G Small Form-Factor Pluggable (SFP+) MSA Compliant
- SFF-8472 Digital Diagnostic Function (DMI)
- SFF-8431 and SFF-8432 Compliant
- Maximum link length of 80 km
- Single +3.3 V Power Supply
- Up to 10.5 Gbps bidirectional data links
- RoHS Compliant
- Compliant with 10GBase-ZX
- Compliant with 1000Base-ZR



tde[®] trans data elektronik GmbH

Hausanschrift:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Vertriebsbüro:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

10Gbase-ZR/1000Base-ZX, SFP+ with DMI 1530nm single mode (LC) [80km/49.7 mi.] Link Budget:
22.0 dB

Technische Daten

Standards

- IEEE 802.3ae
- IEEE 802.3z

Data Rates

- 10.3 Gbps / 1.25 Gbps

Dimensions

- Width: 0.52" [13 mm]
- Depth: 2.2" [56 mm]
- Height: 0.33" [8 mm]

Power Supply

- +3.3V

Environment

- Operating: 0°C to 70°C
- Storage: -40°C to 85°C

Certifications

- IEC-60825, FAD 21, CFR 1040.10 and 1040.11

Warranty

- Lifetime

10Gbase-ZR/1000Base-ZX, SFP+ with DMI 1530nm single mode (LC) [80km/49.7 mi.] Link Budget:
22.0 dB

Artikelvarianten & Zubehör

Art.-Nr.	Beschreibung
TN-10GSFP-LR8M-C53	10Gbase-ZR/1000Base-ZX, SFP+ with DMI 1530nm single mode (LC) [80km/49.7 mi.] Link Budget: 22.0 dB