

10GBase-ZR/1000Base-ZX, SFP+ with DMI single mode (LC) 1531.90nm 195.70THZ [80 km/49.7 mi.]

Link Budget: 22.0 dB



Lantronix / Transition Networks

Features

- SFP+ Optical Transceiver with duplex LC connector
- 1G/10G Small Form-Factor Pluggable (SFP+) MSA compliant
- Compliant with 10GBase-ER/ZR
- Compliant with 1000Base-LX/ZX
- SFF-8472 Digital Diagnostic Function (DMI)
- SFF-8431 and SFF-8432 Compliant
- Maximum Link Length of 80KM
- Single +3.3 V Power Supply
- Lower power dissipation < 1.5 Watts
- RoHS Compliant



tde[®] trans data elektronik GmbH

Hausanschrift:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Vertriebsbüro:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

10GBase-ZR/1000Base-ZX, SFP+ with DMI single mode (LC) 1531.90nm 195.70THZ [80 km/49.7 mi.]

Link Budget: 22.0 dB

Technische Daten

Standards

- IEEE 802.3
- IEEE 802.3ae
- IEEE 802.3z

Dimensions

- Width: 0.52" [13 mm]
- Depth: 2.18" [55 mm]
- Height: 0.33" [8 mm]

Power Input

- 3.3V

Environment

- Operating: 0°C to 70°C
- Operating: -40°C to 85°C

Certifications

- IEC 60825-1, FDA CDRH 21-CFR 1040.10 Class 1

Warranty

- Lifetime

Artikelvarianten & Zubehör

Art.-Nr.	Beschreibung
TN-10GSFP-LR8M-D57	10GBase-ZR/1000Base-ZX, SFP+ with DMI single mode (LC) 1531.90nm 195.70THZ [80 km/49.7 mi.] Link Budget: 22.0 dB