

## LWL-Nummernschlüssel für Patch- und Trunkkabel

Beispielnummer: L-LC/MP50B12G4-00200

L- SSSS / SSSS FF KKKKKK B XXXXX

### Stecker 1/ 2:

<b>BN</b>	Mini BNC
<b>DI</b>	DIN
<b>DIA</b>	DIN APC
<b>E2</b>	E2000
<b>E2A</b>	E2000 APC
<b>E2AC</b>	E2000 APC Compact
<b>E2AP</b>	E2000 APC Premium (0.1 dB)
<b>E2C</b>	E2000 Compact
<b>E2U</b>	E2000 UPC
<b>E2UC</b>	E2000 Compact UPC
<b>ES</b>	Escon (Duplex)
<b>FC</b>	FC
<b>FCA</b>	FC APC
<b>FCU</b>	FC UPC
<b>FS</b>	FSMA
<b>HM</b>	2 bzw. 4 Kanal Plug, HEBM
<b>HMF</b>	2 bzw. 4 Kanal, HEBM Flange Nut Bulkhead
<b>HMJ</b>	2 bzw. 4 Kanal, HEBM Jam Nut Bulkhead
<b>HS</b>	4 Kanal Plug, HEBS
<b>HSJ</b>	4 Kanal, HEBS Jam Nut Bulkhead
<b>HSX</b>	4 Kanal XLR, HEBS
<b>HXL</b>	2 Kanal Plug, HEBXL
<b>HXLF</b>	2 bzw. 12 Kanal, HEBXL Flange Nut Bulkhead
<b>HXLJ</b>	2 bzw. 12 Kanal, HEBXL Jam Nut Bulkhead
<b>LC</b>	LC
<b>LCA</b>	LC APC
<b>LCU</b>	LC UPC
<b>LCJ</b>	LC ODVA Buchse (Duplex)
<b>LCP</b>	LC ODVA Stecker (Duplex)
<b>MI</b>	FDDI (Duplex)
<b>M2</b>	MPO24 Female
<b>M2P</b>	MPO24 Male
<b>MP</b>	MPO12 Female
<b>MPP</b>	MPO12 Male
<b>MT</b>	MT-RJ Female
<b>MT-P</b>	MT-RJ Male
<b>MU</b>	MU
<b>MUU</b>	MU UPC
<b>SC</b>	SC
<b>SCA</b>	SC APC
<b>SCR</b>	SC RJ
<b>SCU</b>	SC UPC
<b>SLC</b>	LC Secure (Duplex)
<b>ST</b>	ST
<b>TLC</b>	LC HD

### Fasertyp:

**09** 9/125µ  
**50** 50/125µ  
**62** 62.5µ/125µ

### MPO/MTP®

#### Belegung:

**A** Typ A  
**B** Typ B  
**C** Typ C

### Länge in cm:

**00050** 0.5 m  
**00100** 1.0 m  
 ... ..

### Kabeltyp:

<b>D</b>	Duplex
<b>D3-</b>	Duplex OM3
<b>D4-</b>	Duplex OM4
<b>D-M</b>	Duplex MiniZip
<b>D3M</b>	Duplex MiniZip OM3
<b>D4M</b>	Duplex MiniZip OM4
<b>S</b>	Simplex
<b>S3-</b>	Simplex OM3
<b>S4-</b>	Simplex OM4
<b>S-M</b>	Simplex MiniZip
<b>S3M</b>	Simplex MiniZip OM3
<b>S4M</b>	Simplex MiniZip OM4
<b>TD</b>	FlatTwin
<b>TD3-</b>	FlatTwin OM3
<b>TD4-</b>	FlatTwin OM4
<b>I12E</b>	Rundkabel SM (12)
<b>I12G</b>	Rundkabel MM OM2 (12)
<b>I12G3-</b>	Rundkabel MM OM3 (12)
<b>I12G4-</b>	Rundkabel MM OM4 (12)
<b>I24G3-</b>	Rundkabel MM OM3 (24)
<b>I24G4-</b>	Rundkabel MM OM4 (24)
<b>B_E</b>	Universalkabel SM (04 - 144)
<b>B_G</b>	Universalkabel MM OM2 (04 - 144)
<b>B_G3-</b>	Universalkabel MM OM3 (04 - 144)
<b>B_G4-</b>	Universalkabel MM OM4 (04 - 144)
<b>P_E</b>	Mil-Tac Breakoutkabel SM (02 - 04)
<b>P_G</b>	Mil-Tac Breakoutkabel MM (02 - 04)
<b>V_E</b>	Breakoutkabel SM (04 - 24)
<b>V_G</b>	Breakoutkabel MM (04 - 24)
<b>V_G3-</b>	Breakoutkabel MM (04 - 24)
<b>V_G4-</b>	Breakoutkabel MM (04 - 24)

\* -

\*Anzahl der Fasern gemäß  
Kabeltypbeschreibung auswählen