TRANSCEIVER- SFP+, CC, 10GBASE-LRM, 1310nm, 10.3G, MM LC, 220M, 3.3V, DMI

Direct Attach Cables / Active Optical Cables

A simple to install, cost-effective and interoperable solution

Often used for data center short-reach interconnects, Direct Attach, Active Copper and Active Optical Cables are an indispensable part of any network.

Terminated with transceiver-style connectors, they are designed to be used in the same ports as a typical SFP+ or QSFP transceiver, with no need for adapters or converters. Our DAC and AOC cables offer compatibility with a huge range of vendors, enabling the connectivity you need within the Top of Rack and End of Row environments.

- 10G, 25G, 40G & 100G product solutions
- Seamless interoperability with network equipment
- Multi-code options enabling different OEM vendors at each end of the cable
- 4x breakout cables, 40G QSFP+ to 4x 10G SFP and 100G QSFP28 to 4x 25G SFP28
- Fast Delivery, Custom solutions
- Compatible with Over 90 Systems
- Savings of up to 70%

10GBase-LRM, SFP+ with DMI, 1310nm multimode (Duplex LC) [220m; 722 ft.] Link Budget: 1.5 dB

Product Description

10GBase-LRM, SFP+ with DMI, 1310nm multimode (Duplex LC) [220m; 722 ft.] Link Budget: 1.5 dB

Features

- SFP+ Optical Transceiver with LC connector
- 10G Small Form-Factor Pluggable (SFP+) MSA compatible
- Compliant with IEEE 802.3ae 10GBase-SR/LR/LW
- SFF-8472 Digital Diagnostic Function (DMI)
- Single +3.3V Power Supply
- RoHS Compliant
- Class 1 Laser International Safety Standard IEC 60825 Compliant

Show product on manufacturers website: https://www.lantronix.com/products/

tde® trans data elektronik GmbH

Hausanschrift:
Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Vertriebsbüro:
Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

 © tde GmbH, alle Rechte vorbehalten, Irrtümer vorbehalten.

TRANSCEIVER- SFP+, CC, 10GBASE-LRM, 1310nm, 10.3G, MM LC, 220M, 3.3V, DMI

Technische Daten

Specifications

Artikelvarianten & Zubehör

Art.-Nr.	Beschreibung
TN-SFP-10G-LRM	TRANSCEIVER- SFP+, CC, 10GBASE-LRM, 1310nm, 10.3G, MM LC, 220M, 3.3V, DMI

© tde GmbH, alle Rechte vorbehalten, Irrtümer vorbehalten.