

## tML<sup>®</sup> - Cable Mounting Bracket Breakout 6fold for Rack Mount Enclosures 1U



### tML<sup>®</sup> tde Modular Link

tML<sup>®</sup> is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site – especially in data centres, but also in industrial environments – within the shortest possible time. Heart of the system are the rear MPO/MTP<sup>®</sup> and Telco connectors, which can be used to connect at least six or twelve ports at a time. Depending on the module configuration, transfer rates of up to 400G are currently possible with SR4. The fibre optic and TP modules can be used together in a module carrier with a very high port density. The tde offers its tML<sup>®</sup> cabling system as a proven tML<sup>®</sup> standard system and in the highly innovative variants tML<sup>®</sup> 12, tML<sup>®</sup> 24, tML<sup>®</sup> 32 and now tML<sup>®</sup> 24+ System for extreme scalability and very easy migration to higher transmission rates such as 40G, 100G, 200G, 400G and 800G and more.

With the tML<sup>®</sup>- Rack Mount Enclosure 19"/1U can do four and with the 10"/1U two Cable Mounting Brackets to be used.



#### tde<sup>®</sup> trans data elektronik GmbH

##### Headquarter address:

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

##### Sales office address:

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 8805 61 13  
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

## tML<sup>®</sup> - Cable Mounting Bracket Breakout 6fold for Rack Mount Enclosures 1U

### Technical Data

Material	galvanized steel sheet
Mounting method	Assembly back at the tML <sup>®</sup> - Rack Mount Enclosure with two which are attached screws.
	QS-Managementsystem ISO 9001, ISO 14001 and TL 9000

### Product variants & accessories

Art.-No.	Description
TML-10/1HE-4-M	tML <sup>®</sup> - Rack Mount Enclosures 10"/1U stainless steel frontplate for 4 x modules
TML-10/1HE-4-M-S	tML <sup>®</sup> - Rack Mount Enclosures 10"/1U black frontplate for 4 x modules
TML-19/1HE-8-CO	tML <sup>®</sup> - Cover for Rack Mount Enclosures 19"/1U
TML-19/1HE-8-M	tML <sup>®</sup> - Rack Mount Enclosures 19"/1U stainless steel frontplate for 8 x modules
TML-19/1HE-8-M-S	tML <sup>®</sup> - Rack Mount Enclosures 19"/1U black frontplate for 8 x modules
TML-K-B-6	tML <sup>®</sup> - Cable Mounting Bracket Breakout 6fold for Rack Mount Enclosures 1U