

## MPO/MTP<sup>®</sup> Adapter without Flange, Type B, grey



### F0 Components

- One piece adapter design maximizes coupling strength while minimizing debris generation
- All adapters compatible with MTP Elite<sup>®</sup> brand connectors and standard grade MTP<sup>®</sup> brand connectors
- Available in black, aqua, beige, green, blue and gray
- Supplied with either one or two thermoplastic non-debris generating dust plugs
- Compatible with all US Conec MTP<sup>®</sup> brand connectors in fiber counts ranging from 4 to 72
- Optimal coarse alignment to minimize pin to ferrule debris generation

### Applications

- Array trunk cabling
- Array fiber to single fiber cassettes
- High fiber density card edge access
- Optical switching interframe connections
- Meets IEC Standard 61754-7



**tde<sup>®</sup>** trans data elektronik GmbH

**Headquarter address:**

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

**Sales office address:**

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 8805 61 13  
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

## MPO/MTP® Adapter without Flange, Type B, grey

- Meets TIA/EIA 604-5 Type MPO
- Structured cabling per TIA-568-C
- Parallel Optics
- Optical Internetworking Forum (OIF) Compliant
- Infiniband Compliant
- 10G Fiber Channel Compliant
- 40G and 100G IEEE 802.3
- SNAP 12
- POP 4
- QSFP

## Technical Data

|                 |                          |
|-----------------|--------------------------|
| Type            | MPO/MTP®                 |
| Application     | Multimode OM1/OM2        |
| Design          | without Flange           |
| Connector style | SC Simplex               |
| Key Orientation | Type B, Key up/up        |
| Color           | Grey                     |
| Material        | Plastic                  |
| Sleeve          | --                       |
| Shutter         | --                       |
| Standards       | IEC 61754-7<br>TIA 604-5 |
| Manufacturer    | US Conec                 |

## Product variants & accessories

| Art.-No.         | Description                                          |
|------------------|------------------------------------------------------|
| L-AD-MPO-NF-A-BG | MPO/MTP® Adapter without Flange, Type A, beige       |
| L-AD-MPO-NF-A-BL | MPO/MTP® Adapter without Flange, Type A, blue        |
| L-AD-MPO-NF-A-GN | MPO/MTP® Adapter without Flange, Type A, green (APC) |
| L-AD-MPO-NF-A-GR | MPO/MTP® Adapter without Flange, Type A, grey        |
| L-AD-MPO-NF-A-SW | MPO/MTP® Adapter without Flange, Type A, black       |
| L-AD-MPO-NF-A-TK | MPO/MTP® Adapter without Flange, Type A, aqua        |
| L-AD-MPO-NF-A-VI | MPO/MTP® Adapter without Flange, Type A, magenta     |
| L-AD-MPO-NF-B-GR | MPO/MTP® Adapter without Flange, Type B, grey        |