


MPO/MTP® Adapter without Flange, Type A, magenta



F0 Components

- One piece adapter design maximizes coupling strength while minimizing debris generation
- All adapters compatible with MTP Elite® brand connectors and standard grade MTP® brand connectors
- Available in black, aqua, beige, green, blue and gray
- Supplied with either one or two thermoplastic non-debris generating dust plugs
- Compatible with all US Conec MTP® brand connectors in fiber counts ranging from 4 to 72
- Optimal coarse alignment to minimize pin to ferrule debris generation

Applications

- Array trunk cabling
- Array fiber to single fiber cassettes
- High fiber density card edge access
- Optical switching interframe connections
- Meets IEC Standard 61754-7



tde® trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

MPO/MTP[®] Adapter without Flange, Type A, magenta

- Meets TIA/EIA 604-5 Type MPO
- Structured cabling per TIA-568-C
- Parallel Optics
- Optical Internetworking Forum (OIF) Compliant
- Infiniband Compliant
- 10G Fiber Channel Compliant
- 40G and 100G IEEE 802.3
- SNAP 12
- POP 4
- QSFP

Technical Data

Type	MPO/MTP [®]
Application	Multimode OM4
Design	without Flange
Connector style	SC Simplex
Key Orientation	Type A, Key up/down
Color	Magenta
Material	Plastic
Sleeve	--
Shutter	--
Standards	IEC 61754-7 TIA 604-5
Manufacturer	US Conec

Product variants & accessories

Art.-No.	Description
L-AD-MPO-NF-A-BG	MPO/MTP [®] Adapter without Flange, Type A, beige
L-AD-MPO-NF-A-BL	MPO/MTP [®] Adapter without Flange, Type A, blue
L-AD-MPO-NF-A-GN	MPO/MTP [®] Adapter without Flange, Type A, green (APC)
L-AD-MPO-NF-A-GR	MPO/MTP [®] Adapter without Flange, Type A, grey
L-AD-MPO-NF-A-SW	MPO/MTP [®] Adapter without Flange, Type A, black
L-AD-MPO-NF-A-TK	MPO/MTP [®] Adapter without Flange, Type A, aqua
L-AD-MPO-NF-A-VI	MPO/MTP [®] Adapter without Flange, Type A, magenta
L-AD-MPO-NF-B-GR	MPO/MTP [®] Adapter without Flange, Type B, grey