


MPO/MTP[®] Adapter with Flange, Type A, grey



F0 Components

- One piece adapter design maximizes coupling strength while minimizing debris generation
- All adapters compatible with MTP Elite[®] brand connectors and standard grade MTP[®] brand connectors
- Available in black, aqua, beige, green, blue and gray
- Supplied with either one or two thermoplastic non-debris generating dust plugs
- Compatible with all US Conec MTP[®] brand connectors in fiber counts ranging from 4 to 72
- Optimal coarse alignment to minimize pin to ferrule debris generation

Applications

- Array trunk cabling
- Array fiber to single fiber cassettes
- High fiber density card edge access
- Optical switching interframe connections
- Meets IEC Standard 61754-7



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

MPO/MTP[®] Adapter with Flange, Type A, grey

- Meets TIA/EIA 604-5 Type MPO
- Structured cabling per TIA-568-C
- Parallel Optics
- Optical Internetworking Forum (OIF) Compliant
- Infiniband Compliant
- 10G Fiber Channel Compliant
- 40G and 100G IEEE 802.3
- SNAP 12
- POP 4
- QSFP

Technical Data

Type	MPO/MTP [®]
Application	Multimode
Design	with Flange
Connector style	MPO/MTP [®]
Key Orientation	Type A, Key up/down
Color	Grey
Material	Plastic
Sleeve	--
Shutter	--
Standards	IEC 61754-7 TIA 604-5
Manufacturer	US Conec

Product variants & accessories

Art.-No.	Description
L-AD-MPO-F-A-BG	MPO/MTP [®] Adapter with Flange, Type A, beige
L-AD-MPO-F-A-BL	MPO/MTP [®] Adapter with Flange, Type A, blue
L-AD-MPO-F-A-GN	MPO/MTP [®] Adapter with Flange, Type A, green (APC)
L-AD-MPO-F-A-GR	MPO/MTP [®] Adapter with Flange, Type A, grey
L-AD-MPO-F-A-SW	MPO/MTP [®] Adapter with Flange, Type A, black
L-AD-MPO-F-A-TK	MPO/MTP [®] Adapter with Flange, Type A, aqua
L-AD-MPO-F-B-GR	MPO/MTP [®] Adapter with Flange, Type B, grey