

tSML - HD FO partial front panel Snap-In with 12x LC Duplex OM4 magenta for tSML Module 0.5U



tSML - tde Semi Modular Link

tSML is a modular developed cabling system, which consists of two core components: module and trunk cable. The system components, preterminated with connectors and tested ex works, facilitate very fast installation of both twisted pair and fiber-optic cables. Ready-made trunk cables, providing a high number of pairs or fibers, can simply be plugged together using patch panels. Up to 96x LC duplex and/or 48 x RJ45 of haven can be accommodated in such a way on 1U. At the heart of the System are MPO/MTP[®] and Telco connectors, with which 12 optical fibers or 24 copper pairs can be connected simultaneously. Fiber-optic and twisted pair modules can be combined on 1U within a panel without difficulty.

The tSML - FO partial front panel is intended for the installation in the tSML Module 0.5U. The tSML HD partial front panel can be used only in conjunction with the tSML HD patch cord.



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

tSML - HD FO partial front panel Snap-In with 12x LC Duplex OM4 magenta for tSML Module 0.5U

Technical Data

Pre-mounted	12 x LC Duplex adapter (magenta)
	QS-Managementsystem ISO 9001, ISO 14001 and TL 9000

tML[®] - partial front panels

Front Panel	Stainless steel
Dimensions	108 x 20 mm

FO Adapters

Type	LC Quad
Application	Multimode OM4
Design	with flange
Footprint	SC Duplex
Color	Magenta
Material	Plastic
Sleeve	Zirkonia Staight Split
Shutter	--
Manufacturer	tde

Product variants & accessories

Art.-No.	Description
TSML-M12LCD-BG	tSML - HD FO partial front panel Snap-In with 12x LC Duplex OM2 beige for tSML Module 0.5U
TSML-M12LCD-BL	tSML - HD FO partial front panel Snap-In with 12x LC Duplex OS2 blue for tSML Module 0.5U
TSML-M12LCD-GN	tSML - HD FO partial front panel Snap-In with 12x LC Duplex OS2 green for tSML Module 0.5U
TSML-M12LCD-TK	tSML - HD FO partial front panel Snap-In with 12x LC Duplex OM3 aqua for tSML Module 0.5U
TSML-M12LCD-VI	tSML - HD FO partial front panel Snap-In with 12x LC Duplex OM4 magenta for tSML Module 0.5U