

tBL[®] - Breakout Panel 19"/0.5U straight blank w/o cover for 4x RJ45 DC 6fold 10GbE



tBL[®] - tde Basic Link (TP)

tBL[®] tde Basic Link (TP) is a complete system solution for structured cabling in Cat6A for transfer rates of up to 10GbE in real time. The tBL[®] - cabling link corresponds to a permanent link in accordance with ISO / IEC 11801 (EN 50173). The RJ45 modules are available in the form factors Keystone (KS) and Data Center (DC). The compact design of the 6fold RJ45 DC module allows a high packing density of up to 48 RJ45 ports on 1U. The RJ45 module is connected to the tBL[®] - cable termination block by simply plugging. The slim cable termination block can be easily assembled on the cable by using the tBL[®] - crimp tool and is suitable for preterminated cables. The modular design of individual RJ45 modules are interchangeable at any time without termination. The RJ45 modules are optional with a LID - Light ID function available. This feature facilitates searching of related ports within a cable link. A cost effective alternative product is the RJ45 keystone module without cable termination block in the tool-less design.

The system solution is complemented by an extensive portfolio of carrier systems. These include design-capable data outlets, floor box frames, Consolidation points, DIN rail modules and patch panels in 1/2 and 1U.



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

tBL[®] - Breakout Panel 19"/0.5U straight blank w/o cover for 4x RJ45 DC 6fold 10GbE

Technical Data

Box	stainless steel
Front plate	stainless steel
Mounting	Snap-In (4x RJ45 DC 6er Modules 10GbE)
Cable strain relief	Breakout cable entries, by cable ties
Dimensions	19", 0.5U, depth 11 cm
Identification	silk screen at the front
	19" mounting set enclosed
	QS-Managementsystem ISO 9001, ISO 14001 and TL 9000

Product variants & accessories

Art.-No.	Description
TBL-M-19/0.5HE-KB	tBL [®] - Breakout Panel 19"/0.5U straight blank w/o cover for 4x RJ45 DC 6fold 10GbE
TBL-M-BLIND	tBL [®] - blind plate Snap-In for Breakout Panel 19"/0.5U
TBL-M-COVER	tBL [®] - Cover for Breakout Panel 19"/0.5U straight