

tML[®] - Consolidationpoint-Housing for up to 4x CU- or FO-modules, grey



tML[®] - tde Modular Link

tML[®] is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site - especially in data centres, but also in industrial environments - within the shortest possible time. The system is characterized by highest packing density and highest flexibility during migration to higher transmission rates. Fibre optic and TP modules can be combined in one rack mount enclosure. 96x fibre optics LC Duplex or 96x MPO connectors can be used modularly on a 19-inch height unit. Thanks to its patented polarity and dark fibre modules, the tML system offers the simplest migration options to 100G and more.

- Elegant housing for wall-, ceiling- and floormounting
- FO- and copper applications
- tML[®] compatible
- Construction for various applications
- Cable In- and output (single strain relief) possible



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

tML[®] - Consolidationpoint-Housing for up to 4x CU- or FO-modules, grey

Technical Data

| | |
|-------------|--|
| Housing | For 10", consisting of: bottom tray with strain relief on both sides and cover with dust caps and sealing lips |
| Front panel | for up to 4x CU- or FO-modules |
| Dimensions | 50 x 260 x 300 mm (HxWxD) |
| Material | Steel 1203 |
| Colour | RAL 7035 (grey) |

Product variants & accessories

| Art.-No. | Description |
|--------------------|---|
| TML-CONS10/1HE-GR | tML [®] - Consolidationpoint-Housing for up to 4x CU- or FO-modules, grey |
| TML-CONS10/1HE-SW | tML [®] - Consolidationpoint-Housing for up to 4x CU- or FO-modules, black |
| TML-CONS19/1HE-GR | tML [®] - Consolidationpoint-Housing for up to 8x CU- or FO-modules, grey |
| TML-CONS19/1HE-SW | tML [®] - Consolidationpoint-Housing for up to 8x CU- or FO-modules, black |
| TML-CONS3HE/8TE-GR | tML [®] - Consolidationpoint-Housing for up to 2x CU- or FO-modules, grey |
| TML-CONS3HE/8TE-SW | tML [®] - Consolidationpoint-Housing for up to 2x CU- or FO-modules, black |