

tBL[®] - FO breakout panel 19" 1U 24x SC Simplex Adapter, aqua



tBL[®] - tde Basic Link (FO Enclosures)

The FO enclosures of the tBL[®] - tde Basic Link series are optimized products with a high functionality and an easy handling at the installation. The program includes splice and breakout boxes for 19 inch, wall and DIN rail mounting. These products are characterized by a high port density and an optimal fiber management, so that the permissible bending radii can't be undercut. Moreover, there are no sharp corners or edges, to avoid damage to the pigtailed and buffer tubes. The front plates are removable. There are versions for E2000, FC, PC, LC, MPO / MTP, MTRJ, MU, SC, and ST. These products can be obtained with or without equipment. In addition, there are also special versions with IP66 for outdoor and offshore applications.



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

tBL[®] - FO breakout panel 19" 1U 24x SC Simplex Adapter, aqua

Technical Data

| | |
|-------------------------|--------------------------------|
| Alternative pre-mounted | TBL-PF24-xxSCS-TK (see below) |
| xx | (01 - 24) quantity of adapters |

FO Splice Boxes

| | |
|---------------|--|
| Type | Breakout panel with cable catch |
| Material | Sheet steel |
| Color | RAL 7035 |
| Dimensions | 19" 1U 240mm depth |
| Labeling | 1 - 24 (silk screen) |
| Configuration | Attachment up to 24x SC Simplex, LC Duplex, E2000 Simplex or MPO adapter |

FO Adapters

| | |
|-----------------|-------------------------|
| Type | SC Simplex |
| Application | Multimode OM3 |
| Design | with flange |
| Connector style | SC Simplex |
| Color | Aqua |
| Material | Plastik |
| Sleeve | Zirkonia Straight Split |
| Shutter | -- |
| Manufacturer | tde |

| | |
|------|---------------------------------|
| Type | Mounting set M5 |
| | Set of 4 (cage nuts and screws) |

Product variants & accessories

| Art.-No. | Description |
|--------------------|---|
| TBL-PF24-24SCAS-GN | tBL [®] - FO breakout panel 19" 1U 24x SC Simplex Adapter, green APC |
| TBL-PF24-24SCS-BG | tBL [®] - FO breakout panel 19" 1U 24x SC Simplex Adapter, beige |
| TBL-PF24-24SCS-BL | tBL [®] - FO breakout panel 19" 1U 24x SC Simplex Adapter, blue |
| TBL-PF24-24SCS-TK | tBL [®] - FO breakout panel 19" 1U 24x SC Simplex Adapter, aqua |
| TBL-PF24-24SCS-VI | tBL [®] - FO breakout panel 19" 1U 24x SC Simplex Adapter, magenta |