


tBL® - FO breakout panel 19" 1U 12x LC Duplex Adapter, green APC



tBL® - tde Basic Link (FO Enclosures)

The FO enclosures of the tBL® - tde Basic Link series are optimized products with a high functionality and an easy handling at the installation. The program includes splice and breakout boxes for 19 inch, wall and DIN rail mounting. These products are characterized by a high port density and an optimal fiber management, so that the permissible bending radii can't be undercut. Moreover, there are no sharp corners or edges, to avoid damage to the pigtails and buffer tubes. The front plates are removable. There are versions for E2000, FC, PC, LC, MPO / MTP, MTRJ, MU, SC, and ST. These products can be obtained with or without equipment. In addition, there are also special versions with IP66 for outdoor and offshore applications.



tde® trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

tBL® - FO breakout panel 19" 1U 12x LC Duplex Adapter, green APC

Technical Data

Alternative pre-mounted	TBL-PF24-xxLCAD-GN (see below)
xx	(01 - 24) quantity of adapters

FO Splice Boxes

Type	Breakout panel with cable catch
Material	Sheet steel
Color	RAL 7035
Dimensions	19" 1U 240mm depth
Labeling	1 - 24 (silk screen)
Configuration	Attachment up to 24x SC Simplex, LC Duplex, E2000 Simplex or MPO adapter

FO Adapters

Type	LC Duplex
Application	Singlemode OS2 APC
Design	One-Piece with flange
Connector style	SC Simplex
Color	Green
Material	Plastic
Sleeve	Zirconia Straight Split
Shutter	-
Manufacturer	tde

Type	FO Blind stopper
Application	For covering of unused adapter slots

Type	Mounting set M5
	Set of 4 (cage nuts and screws)

Product variants & accessories

Art.-No.	Description
TBL-PF24-12LCAD-GN	tBL® - FO breakout panel 19" 1U 12x LC Duplex Adapter, green APC
TBL-PF24-12LCD-BG	tBL® - FO breakout panel 19" 1U 12x LC Duplex Adapter, beige
TBL-PF24-12LCD-TK	tBL® - FO breakout panel 19" 1U 12x LC Duplex Adapter, aqua
TBL-PF24-12LCD-VI	tBL® - FO breakout panel 19" 1U 12x LC Duplex Adapter, magenta