

Managed 10 Gigabit Ethernet Access/Aggregation Switch, (24) 100/1000Base SFP Ports + (4) 1000Base/10GBase SFP+ Ports



(24) 100/1000Base SFP ports with

(4) 1000Base/10G SFP+ ports

Includes 19" Rack Mount ears

## Description

Transition Networks' Carrier Ethernet solution delivers the promise of simplicity deployed. This comprehensive solution includes CE 2.0 compliant demarcation devices, access switches, and the Converge™ element and service management platform.

With the goal of enabling new service generating revenue, Transition Networks' S4224 access switch with (24) 100/1000Base SFP ports and (4) 1000Base/10G uplinks is designed to support a wide range of MEF-based Carrier Ethernet services for Mobile Backhaul, Business Ethernet, Cloud Assurance and Carrier Exchange E-Access Services.

## Features



**tde<sup>®</sup>** trans data elektronik GmbH

### Hausanschrift:

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

### Vertriebsbüro:

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 914 36 99  
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

## Managed 10 Gigabit Ethernet Access/Aggregation Switch, (24) 100/1000Base SFP Ports + (4) 1000Base/10GBase SFP+ Ports

- (24) 100/1000Base SFP ports
- (4) 1000/10GBase Dual Speed SFP+ ports; Any port can be network or client
- E-Line (EPL and EVPL) E-LAN (EP-LAN and EVP-LAN) E-Access (Access EPL and EVPL)
- Blended Ethernet Service Activation testing supporting RFC2544 and "services" testing via EVC bandwidth policies or CoS ingress and egress tags with 1-way delay measurements reported in 1-milliseconds
- Hardware based Precision Time Protocol 1588v2 with clock off-set reporting and monitoring between grandmaster and slave with nanosecond accuracy.
- Multi-CoS 802.1p and IPv4/IPv6 DiffServ/TOS to ensure any level of service between operator and customer networks
- Hardware based Service OAM (IEEE 802.1ag) and Performance Monitoring (ITU Y.1731) ensure accurate service performance delivery with two and one-way delay measurement reporting.

Show product on manufacturers website: <https://www.transition.com/products/switch/s4224-series/>

## Technische Daten

## Specifications

## Artikelvarianten & Zubehör

Art.-Nr.	Beschreibung
S4224	Managed 10 Gigabit Ethernet Access/Aggregation Switch, (24) 100/1000Base SFP Ports + (4) 1000Base/10GBase SFP+ Ports