

Unmanaged Hardened Fast Ethernet Switch, (5) 10/100Base-TX Ports or (8) 10/100Base-TX Ports



Direct Attach Cables / Active Optical Cables

A simple to install, cost-effective and interoperable solution

Often used for data center short-reach interconnects, Direct Attach, Active Copper and Active Optical Cables are an indispensable part of any network.

Terminated with transceiver-style connectors, they are designed to be used in the same ports as a typical SFP+ or QSFP transceiver, with no need for adapters or converters. Our DAC and AOC cables offer compatibility with a huge range of vendors, enabling the connectivity you need within the Top of Rack and End of Row environments.

- 10G, 25G, 40G & 100G product solutions
- Seamless interoperability with network equipment
- Multi-code options enabling different OEM vendors at each end of the cable
- 4x breakout cables, 40G QSFP+ to 4x 10G SFP and 100G QSFP28 to 4x 25G SFP28
- Fast Delivery, Custom solutions
- Compatible with Over 90 Systems
- Savings of up to 70%



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

Unmanaged Hardened Fast Ethernet Switch, (5) 10/100Base-TX Ports or (8) 10/100Base-TX Ports

(8) 10/100Base-TX (RJ-45) [100 m/328 ft.]

Description

The SISTF1010-2x0-LRT Fast Ethernet switch family contains simple "Plug-and-Play" multi-port switches of either (5) or (8) ports. This switch family is best used at the edge of a hardened network to provide connections for devices in hazardous locations.

Features

- Auto-Negotiation
- Auto-MDI/MDIX
- Store-and-Forward Switching Architecture with MAC Address Table
- Extended operating temperature (-40°C to 75°C)
- Dry Contact Relay Alarm Output
- Dual, Redundant DC Power Inputs
- DIN Rail Mounting and Wall Mount Brackets Included
- Reverse Polarity Power Input Protection
- Overload Current Protection
- Barrel connector interface cable included for connecting external AC/DC power supply
- Class 1, Div 2 Certified

Show product on manufacturers website: <https://www.lantronix.com/products/>

Technical Data

Specifications

Product variants & accessories

Art.-No.	Description
SISTF1010-280-LRT	Unmanaged Hardened Fast Ethernet Switch, (5) 10/100Base-TX Ports or (8) 10/100Base-TX Ports