TRANSCEIVER- SFP, JP, 100BASE-FX, 1310, MM LC, 2km, 3.3V, @ Giga SFP Port



Direct Attach Cables / Active Optical Cables

A simple to install, cost-effective and interoperable solution

Often used for data center short-reach interconnects, Direct Attach, Active Copper and Active Optical Cables are an indispensable part of any network.

Terminated with transceiver-style connectors, they are designed to be used in the same ports as a typical SFP+ or QSFP transceiver, with no need for adapters or converters. Our DAC and AOC cables offer compatibility with a huge range of vendors, enabling the connectivity you need within the Top of Rack and End of Row environments.

- 10G, 25G, 40G & 100G product solutions
- Seamless interoperability with network equipment
- Multi-code options enabling different OEM vendors at each end of the cable
- 4x breakout cables, 40G QSFP+ to 4x 10G SFP and 100G QSFP28 to 4x 25G SFP28
- Fast Delivery, Custom solutions
- Compatible with Over 90 Systems
- Savings of up to 70%

tde® trans data elektronik GmbH

Headquarter address:
Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:
Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

 © tde GmbH, all rights reserved, errors excepted.

TRANSCEIVER- SFP, JP, 100BASE-FX, 1310, MM LC, 2km, 3.3V, @ Giga SFP Port

100Base-FX 1310nm (Duplex LC) multimode [2 km/1.24 mi.] Link Budget: 8.0 dB

Product Description

100Base-FX 1310nm (Duplex LC) multimode [2 km/1.24 mi.] Link Budget: 8.0 dB

Features

- Small Form-Factor Pluggable (SFP) MSA compatible
- Compliant with IEEE 802.3z 1000Base-SX/LX
- Compliant with IEEE 802.3 100Base-FX
- Single +3.3V Power Supply
- RoHS Compliant
- Class 1 Laser International Safety Standard EC 60825 Compliant

Show product on manufacturers website: https://www.lantronix.com/products/

Technical Data

Specifications

Product variants & accessories

Art.-No.	Description
TN-JX-GE-100FX	TRANSCEIVER- SFP, JP, 100BASE-FX, 1310, MM LC, 2km, 3.3V, @ Giga SFP Port

© tde GmbH, all rights reserved, errors excepted.