

TRANSCEIVER- SFP, LX, 1.25GIG, FIBER, LC, 50KM, W/DMI

## Direct Attach Cables / Active Optical Cables

A simple to install, cost-effective and interoperable solution

Often used for data center short-reach interconnects, Direct Attach, Active Copper and Active Optical Cables are an indispensable part of any network.

Terminated with transceiver-style connectors, they are designed to be used in the same ports as a typical SFP+ or QSFP transceiver, with no need for adapters or converters. Our DAC and AOC cables offer compatibility with a huge range of vendors, enabling the connectivity you need within the Top of Rack and End of Row environments.

- 10G, 25G, 40G & 100G product solutions
- Seamless interoperability with network equipment
- Multi-code options enabling different OEM vendors at each end of the cable
- 4x breakout cables, 40G QSFP+ to 4x 10G SFP and 100G QSFP28 to 4x 25G SFP28
- Fast Delivery, Custom solutions
- Compatible with Over 90 Systems
- Savings of up to 70%

1000Base-LX 1550nm single mode (Duplex LC) with DMI [50 km/31.1 mi.] Link Budget: 19.0 dB

## Product Description

1000Base-LX 1550nm single mode (Duplex LC) with DMI [50 km/31.1 mi.]

Link Budget: 19.0 dB

## Features

- Hot-Pluggable SFP Footprint Optical Transceiver
- Digital Diagnostic Function
- Class 1 Laser International Safety Standard IEC-60825 Compliant
- Compatible with SFP Multi-Sourcing Agreement (MSA)

Show product on manufacturers website: <https://www.lantronix.com/products/>



**tde<sup>®</sup>** trans data elektronik GmbH

### Hausanschrift:

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

### Vertriebsbüro:

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 8805 61 13  
Fax.: +49 231 8805 61 15

[info@tde.de](mailto:info@tde.de) | [www.tde.de](http://www.tde.de)

TRANSCEIVER- SFP, LX, 1.25GIG, FIBER, LC, 50KM, W/DMI

## Technische Daten

## Specifications

## Artikelvarianten & Zubehör

| Art.-Nr.   | Beschreibung                                          |
|------------|-------------------------------------------------------|
| TN-SFP-LX5 | TRANSCEIVER- SFP, LX, 1.25GIG, FIBER, LC, 50KM, W/DMI |