


tML[®] - partial front panel with 6x LC Duplex SM green for Rack Mount Enclosure 1U extendable



tML[®] 24

tML[®] 24 is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site – especially in data centres, but also in industrial environments – within the shortest possible time. Heart of the system are the rear MPO/MTP[®] 24 fiber and Telco connectors, which can be used to connect at least six or twelve ports at a time. Depending on the module configuration, transfer rates of up to 400G are currently possible with SR4. The fibre optic and TP modules can be used together in a module carrier with a very high port density. The tde offers its tML[®] cabling system as a proven tML[®] standard system and in the highly innovative variants tML[®]Xtended and now tML[®] 32 for extreme scalability and very easy migration to higher transmission rates such as 40G, 100G, 200G and 400G.

The tML[®] - FO partial front panel is intended for the installation in the tML[®] Rack Mount Enclosure 1U extendable (for 8 x Modules).



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

tML[®] - partial front panel with 6x LC Duplex SM green for Rack Mount Enclosure 1U extendable

Technical Data

Pre-mounted	6 x LC Duplex adapter (green)
	QS-Managementsystem ISO 9001, ISO 14001 and TL 9000

Box	Galvanized steel sheet
Front Panel	Stainless steel
Dimensions	110 x 108 x 20 mm

F0 Adapters

Type	LC Duplex
Application	Singlemode OS2 APC
Design	One-Piece without flange
Connector style	SC Simplex
Color	Green
Material	Plastic
Sleeve	Zirkonia Staight Split
Shutter	--
Manufacturer	tde

Product variants & accessories

Art.-No.	Description
TML-M06LCDH-BL-A8	tML [®] - partial front panel with 6x LC Duplex SM blau for Rack Mount Enclosure 1U extendable
TML-M06LCDH-GN-A8	tML [®] - partial front panel with 6x LC Duplex SM green for Rack Mount Enclosure 1U extendable
TML-M06LCDH-TK-A8	tML [®] - partial front panel with 6x LC Duplex OM3 aqua for Rack Mount Enclosure 1U extendable
TML-M06LCDH-VI-A8	tML [®] - partial front panel with 6x LC Duplex OM4 magenta for Rack Mount Enclosure 1U extendable
TML-M06LCDS-LG-A8	tML [®] - partial front panel with 6x LC Duplex w. shutter OM5 limegreen for Rack Mount Enclosure 1U extendable