RS232 (DTE) 5V,STANDALONE,SC MM W/EU PS

Direct Attach Cables / Active Optical Cables

A simple to install, cost-effective and interoperable solution

Often used for data center short-reach interconnects, Direct Attach, Active Copper and Active Optical Cables are an indispensable part of any network.

Terminated with transceiver-style connectors, they are designed to be used in the same ports as a typical SFP+ or QSFP transceiver, with no need for adapters or converters. Our DAC and AOC cables offer compatibility with a huge range of vendors, enabling the connectivity you need within the Top of Rack and End of Row environments.

- 10G, 25G, 40G & 100G product solutions
- Seamless interoperability with network equipment
- Multi-code options enabling different OEM vendors at each end of the cable
- 4x breakout cables, 40G QSFP+ to 4x 10G SFP and 100G QSFP28 to 4x 25G SFP28
- Fast Delivery, Custom solutions
- Compatible with Over 90 Systems
- Savings of up to 70%

DB-9 (male) [15 m/49 ft.]

to 1300nm multimode (SC) [2 km/1.2 mi.]

Link Budget: 11.0 dB

Description

Link a remote terminal to a host computer: Connect multiple devices, such as security scanners, POS devices, remote terminals and building access/alarming systems to a host computer. Ideal for campus or business environments where remote devices can be networked in a point-to-point configuration where distances are greater than the 15 meter limitation of conventional copper serial cables.

Transition Networksâ Just Convert It serial RS232 to Fiber Media Converter is an inexpensive, no frills way to extend the distance between serial connections with the use of fiber optic cable. This converter supports full or half-duplex data transmission at speeds up to 120 Kbps. Unit and Port LEDs allow for quick status information on the converter.

Features

tde® trans data elektronik GmbH

Headquarter address:
Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:
Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

 © tde GmbH, all rights reserved, errors excepted.

RS232 (DTE) 5V,STANDALONE,SC MM W/EU PS

- Offered with either a male or female connector
- Full/Half-duplex transmission at speeds up to 120 Kbps
- Fiber LED lights to show link with or without data transmission

Show product on manufacturers website: https://www.lantronix.com/products/

Technical Data

Specifications

Product variants & accessories

Art.-No.	Description
J/RS232-TF-01(SC)-EU	RS232 (DTE) 5V,STANDALONE,SC MM W/EU PS

© tde GmbH, all rights reserved, errors excepted.