

tde[®]

trans data elektronik GmbH

net.work.solution. made in Germany

ISO 9001
TL 9000
ISO 14001



tPM tde Patch Cord Management

Professional cable management





tPM tde Patch Cord Management

tPM - tde patch cord management system for an orderly patch cable management with integrated strain relief function. The utility model protected three-part system consists of a 19" Panel, cable guide holders and foam inserts. The cable guide holders can be equipped with different foam inserts and fastened in 17 different positions on the 19" panel. In addition, up to 6 conventional plastic or metal rings can be used. Thus, a wide variety of cable volumes can be handled.

The simple fastening and locking mechanism of the cable guide holder is used without tools. The foam inserts are available with cut-outs for a wide variety of cable types and cable volumes. The carrier plate is prepared for a cover to seal the height unit.

Areas of application :

In every network rack of the application fields:

- > Datacenter
- > Datacom
- > Telecom
- > Industry
- > Defence



Product features

- > Orderly patch cord management
- > Integrated strain relief of the patch cords
- > Compliance with patch cord bending radii
- > No additional loss due to fiber stress
- > Prevents kinking of the cables directly behind the connector boot
- > Horizontal and vertical Patch Cord Management
- > Suitable foam inserts for different cable diameters
- > Ideal for high packing densities
- > Ideal for high availability applications
- > Applicable for FO and TP patch cords.

tPM Patch Cord Management horizontal

Panel with 4x cable guide holders



Description	Part Number
19 inch/1U, without foam inserts	TPM-19/1HE-4-SW

Panel



Description	Part Number
19 inch/1U	TPM-19/1HE-SW

Cover for Panel



Description	Part Number
1U	TPM-19/ 1HE-A

Panel with 2x cable entries and brush strips



Description	Part Number
19 inch/1U	TPM-19/1HE-B-SW

tPM Cable guide holders + foam inserts

Cable guide holder



Description	Part Number
without foam inserts	TPM-KB-SW

Foam insert sawtooth shape flattend



Foam insert sawtooth shape



Description	Part Number
black	TPM-SB06-SW

Foam insert 48 cut-outs Ø 1mm



Description	Part Number
black	TPM-SB48-SW

tPM Patch Cord Management laterally

Panel angled mounting left



Panel angled mounting right



Panel mounting left or right



Description	Part Number
for vertical cable management, without cable guide holders	TPM-1HE-LGV/RGV-SW

tPM Patch Cord Management vertical

Panel vertical 65cm



Description	Part Number
without cable guide holders, without mounting brackets	TPM-V-065-SW

Panel vertical 85cm



Description	Part Number
without cable guide holders, without mounting brackets	TPM-V-085-SW

Mounting bracket set straight



Description	Part Number
2 piece, included fixing screws	TPM-V-AW-SW

Mounting bracket left



Description	Part Number
included fixing screws	TPM-V-LA-SW

Mounting bracket right



Description	Part Number
included fixing screws	TPM-V-RA-SW

Connecting rail



Description	Part Number
included fixing screws	TPM-V-VERB-SW


tPM Accessories

TP Patch Cord Management ring 110mm



Description	Part Number
metal	TPM-RP-BGL-110

TP Patch Cord Management double ring 110mm



Description	Part Number
metal	TPM-RP-BGL-110-DX

FO Patch Cord Management ring 56mm



Description	Part Number
plastic, black	TPM-RP-BGL-56-K

FO Patch Cord Management ring 100mm



Description	Part Number
plastic, black	TPM-RP-BGL-100-K