

## Description

tML® is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site – especially in data centres, but also in industrial environments – within the shortest possible time. Heart of the system are the rear MPO/MTP® and Telco connectors, which can be used to connect at least six or twelve ports at a time. Depending on the module configuration, transfer rates of up to 400G are currently possible with SR4. The fibre optic and TP modules can be used together in a module carrier with a very high port density. The tde offers its tML® cabling system as a proven tML® standard system and in the highly innovative variants tML® 12, tML® 24, tML® 32 and now tML® 24+ System for extreme scalability and very easy migration to higher transmission rates such as 40G, 100G, 200G, 400G and 800G and more.

The tML® - FO Module 5HP MPO/MTP® is intended for the installation in the tML® Rack Mount Enclosure 3U (for 17 x Modules).



## Technical Data

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP® plug has a defined fiber height of 1 - 3.5µ. The max. adjacent fiber height difference is 0.2µm and for all fibers 0.3µm. All system components (modules, trunk cables and patch cords) are co-ordinated for the reaching of the performance particularly. The module is marked with sequential serial number and article number. The modules are ROHS compliant.

|       |  |
|-------|--|
| Entry | 1 x MPO/MTP® Male Adapter (aqua) back  |
| Exit  | 6 x SC Duplex Adapter (aqua) front   |
| Tests | Interferometer, Insertion Loss, Return Loss and Visual Final Inspection; all measured values are electronically archived |
|       | QS-Managementsystem ISO 9001, ISO 14001 and TL 9000  |

|             |                        |
|-------------|------------------------|
| Box         | Galvanized steel sheet |
| Front Panel | black                  |

### FO Adapters

|                 |                          |
|-----------------|--------------------------|
| Type            | MPO/MTP®                 |
| Application     | Multimode OM3            |
| Design          | without Flange           |
| Connector style | SC Simplex               |
| Key Orientation | Type A, Key up/down      |
| Color           | Aqua                     |
| Material        | Plastic                  |
| Sleeve          | --                       |
| Shutter         | --                       |
| Standards       | IEC 61754-7<br>TIA 604-5 |
| Manufacturer    | US Conec                 |

### FO Adapters

|                 |                          |
|-----------------|--------------------------|
| Type            | SC Duplex                |
| Application     | Multimode OM3            |
| Design          | One-Piece without flange |
| Connector style | SC Duplex                |
| Color           | Aqua                     |
| Material        | Plastic                  |
| Sleeve          | Zirconia Straight Split  |
| Shutter         | --                       |
| Manufacturer    | tde                      |

### FO Connectors

|              |  |
|--------------|--|
| Type         | MPO/MTP® Male Push Pull Locking (aqua) |
| Ferrule      | 12 Fiber MM Elite® ferrule, PPS        |
| Boot colour  | Black                                  |
| Manufacturer | tde/US Conec                           |

Optical Performance

| Fiber       | Type     | Wavelength | Insertion loss typ. | Insertion loss max. | Return loss min. |
|-------------|----------|------------|---------------------|---------------------|------------------|
| 50/125µ OM3 | MPO/MTP® | 850 nm     | ≤ 0.14 dB           | 0.25 dB             | 35 dB            |

FO Connectors

|                       |  |
|-----------------------|--|
| Connector Type        | SC Simplex                                     |
| Housing               | Plastic, Aqua                                  |
| Ferrule               | Zirconia Straight Split, Spring-loaded Axially |
| Ferrule Hole          | 126 µ  |
| Mating Cycles         | 1.000  |
| Operating Temperature | -40°C up to +75°C                              |
| Strain Relief to      | 150 N  |
| Manufacturer          | tde  |

Optical performance

| Fiber       | Type | Wavelength | Insertion loss typ. | Insertion loss max. | Return loss min. |
|-------------|------|------------|---------------------|---------------------|------------------|
| 50/125µ OM3 | SC   | 850 nm     | ≤ 0.20 dB           | 0.35 dB             | 30 dB            |

FO Fiber

|                                   |   |
|-----------------------------------|---|
| Type                              | Corning ClearCurve® 50/125µ OM3 multimode fiber   |
| Optimized Data Rate over Distance | 40/100 Gb/s über 140 m*<br>10 Gb/s over 300 m<br>1 Gb/s over 1000 m   |
| Standard Compliance               | ISO/IEC 11801: type OM3 fiber<br>IEC 60793-2-10: type A1a.2 fiber<br>TIA/EIA: 492AAAC-B<br>ITU: ITU G651.1  |
| *                                 | Distances specified in the 40G/100G per IEEE 802.3ba standard are 150m on OM4 and 100m on OM3; Corning fibers are manufactured to tighter dispersion specifications and thereby support the extended distances shown in the table (assuming cable attenuation ≤3.0 dB/km and same 1.0 dB of connector loss for OM3 that the standard requires for OM4). |

Optical Specifications

|           |  |
|-----------|--|
| Bandwidth | High Performance EMB* (MHz.km): 2000 at 850 nm only<br>Legacy Performance EMB* (MHz.km): 1500 at 850 nm / 500 at 1300 nm |
|-----------|--|

|                    |   |
|--------------------|---|
| Attenuation        | At 850 nm max. ≤ 2.3 dB/km<br>At 1300 nm max. ≤ 0.6 dB/km   |
| Macrobend Loss     | Mandrel Radius (mm): 37.5 / 15 / 7.5<br>Number of Turns: 100 / 2 / 2<br>Induced Attenuation (dB) at 850 nm: ≤ 0.05 / ≤ 0.1 / ≤ 0.2<br>Induced Attenuation (dB) at 1300 nm: ≤ 0.15 / ≤ 0.3 / ≤ 0.5 |
| Numerical Aperture | 0.200 ± 0.015   |
| *                  | Ensured via miniEMBc, per TIA/EIA 455-220A and IEC 60793-1-49, for high performance laser-based systems (up to 10 Gb/s).  |
| **                 | OFL BW, per TIA/EIA 455-204 and IEC 60793-1-41, for legacy and LED-based systems (typically up to 100 Mb/s).  |

#### Dimensional Specifications

|                                |                |
|--------------------------------|----------------|
| Core Diameter                  | 50.0 ± 2.5 µm  |
| Cladding Diameter              | 125.0 ± 1.0 µm |
| Core-Clad Concentricity        | ≤ 1.5 µm       |
| Cladding Non-Circularity       | ≤ 1.0%         |
| Core Non-Circularity           | ≤ 5.0%         |
| Coating Diameter               | 242 ± 5 µm     |
| Coating-Cladding Concentricity | < 12 µm        |

#### Environmental

| Environmental Test           | Test Condition                  | Induced Attenuation 850 nm & 1300 nm (dB/km) |
|------------------------------|---------------------------------|--|
| Temperature Dependence       | -60°C to +85°C                  | ≤ 0.10                                       |
| Temperature Humidity Cycling | -10°C to +85°C and 4% to 98% RH | ≤ 0.10                                       |
| Water Immersion              | 23°C ± 2°C                      | ≤ 0.20                                       |
| Heat Aging                   | 85°C ± 2°C                      | ≤ 0.20                                       |
| Damp Heat                    | 85°C at 85% RH                  | ≤ 0.20                                       |
| Operating Temperature Range  | -60°C to +85°C                  |  |

#### Mechanical Specifications

|            |   |
|------------|---|
| Proof Test | The entire fiber length is subjected to a tensile stress ≥ 100 kpsi (0.7 GN/m <sup>2</sup> ). |
| Length     | Fiber lengths available up to 17.6 km/spool.  |

Performance Characterizations

|                                     |  |
|-------------------------------------|--|
| Refractive Index Difference         | 1%   |
| Effective Group Index of Refraction | 850 nm: 1.480<br>1300 nm: 1.479  |
| Fatigue Resistance Parameter (nd)   | 20   |
| Coating Strip Force                 | Dry: 0.6 lbs (2.7N)<br>Wet: 14 days in 23°C water soak: 0.6 lbs (2.7N)   |
| Chromatic Dispersion                | Zero Dispersion Wavelength ( $\lambda_0$ ): 1295 nm $\leq \lambda_0 \leq$ 1315 nm<br>Zero Dispersion Slope (S0): $\leq 0.101$ ps/(nm <sup>2</sup> *km) |

| Art.-No.             | Description   |
|----------------------|---|
| TML-T06SCADK/MPP09ES | tML® - FO Module 5HP black MPO/MTP® with Pins/6x SC APC Duplex 9/125µ OS2 |
| TML-T06SCDK/MPP09ES  | tML® - FO Module 5HP black MPO/MTP® with Pins/6x SC Duplex 9/125µ OS2     |
| TML-T06SCDK/MPP50G3S | tML® - FO Module 5HP black MPO/MTP® with Pins/6x SC Duplex 50/125µ OM3    |
| TML-T06SCDK/MPP50G4S | tML® - FO Module 5HP MPO/MTP® black with Pins/6x SC Duplex 50/125µ OM4    |
| TML-T06SCDK/MPP50GS  | tML® - FO Module 5HP black MPO/MTP® with Pins/6x SC Duplex 50/125µ OM2    |
| TML-T06SCDK/MPP62GS  | tML® - FO Module 5HP black MPO/MTP® with Pins/6x SC Duplex 62,5/125µ OM1  |