

## Description

tML® is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site – especially in data centres, but also in industrial environments – within the shortest possible time. Heart of the system are the rear MPO/MTP® and Telco connectors, which can be used to connect at least six or twelve ports at a time. Depending on the module configuration, transfer rates of up to 400G are currently possible with SR4. The fibre optic and TP modules can be used together in a module carrier with a very high port density. The tde offers its tML® cabling system as a proven tML® standard system and in the highly innovative variants tML® 12, tML® 24, tML® 32 and now tML® 24+ System for extreme scalability and very easy migration to higher transmission rates such as 40G, 100G, 200G, 400G and 800G and more.

The tML® - FO Module MPO/MTP® is intended for the installation in the tML® Rack Mount Enclosure 1U (for 8 x Modules).

## Technical Data

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP® plug has a defined fiber height of 1 - 3.5µ. The max. adjacent fiber height difference is 0.2µm and for all fibers 0.3µm. All system components (modules, trunk cables and patch cords) are co-ordinated for the reaching of the performance particularly. The module is marked with sequential serial number and article number. The modules are ROHS compliant.

Entry	1 x MPO/MTP® Male Adapter (beige) back
Exit	6 x SC Duplex Adapter (beige) front
Tests	Interferometer, Insertion Loss, Return Loss and Visual Final Inspection; all measured values are electronically archived
	QS-Managementsystem ISO 9001, ISO 14001 and TL 9000

Box	Galvanized steel sheet
Front Panel	Stainless steel
Dimensions	110 x 108 x 20 mm

## FO Adapters

Type	MPO/MTP®
Application	Multimode OM1/OM2
Design	without Flange
Connector style	SC Simplex
Key Orientation	Type A, Key up/down
Color	Beige
Material	Plastic

Sleeve	--
Shutter	--
Standards	IEC 61754-7 TIA 604-5
Manufacturer	US Conec

### FO Adapters

Type	SC Duplex
Application	Multimode OM2/OM1
Design	One-Piece with flange
Connector style	SC Duplex
Color	Beige
Material	Plastic
Sleeve	Zirconia Straight Split
Shutter	--
Manufacturer	tde

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP® plug has a defined fiber height of 1 - 3.5µm. The max. adjacent fiber height difference is 0.2µm and for all fibers 0.3µm.

### FO Connectors

Type	MPO/MTP® Male Push Pull Locking with Elite Pins (beige)
Ferrule	12 Fiber MM Elite® ferrule, PPS
Boot colour	Black
Temperature range	-40°C to +75°C
Manufacturer	tde/US Conec

### Optical Performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125µ OM2	MPO/MTP®	850 nm	≤ 0.25 dB	0.45 dB	20 dB
62.5/125µ OM1	MPO/MTP®	850 nm	≤ 0.25 dB	0.45 dB	

### FO Connectors

Connector Type	SC Simplex
----------------	------------

# tML® - FO Module MPO/MTP® with Pins/6x SC Duplex 62,5/125µ OM1

Housing	Plastic, Beige
Ferrule	Zirconia Straight Split, Spring-loaded Axially
Ferrule Hole	126 µ
Mating Cycles	1.000
Operating Temperature	-40°C up to +75°C
Strain Relief to	150 N
Manufacturer	tde

## Optical performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125µ OM2	SC	850 nm	≤ 0.25 dB	0.45 dB	30 dB
62.5/125µ OM1	SC	850 nm	≤ 0.25 dB	0.45 dB	

## FO Fiber

Type	Corning 62.5/125µ OM1 multimode fiber
Manufacturer	Corning

## Optical Specifications

Bandwidth	160/200 at 850 nm / 500 at 1300 nm
Attenuation	At 850 nm max. ≤ 3.0 dB/km At 1300 nm max. ≤ 0.7 dB/km
Numerical Aperture	0.275 ± 0.015

## Dimensional Specifications

Core Diameter	62.5 ± 3.0 µm
Cladding Diameter	125.0 ± 2.0 µm
Core-Clad Concentricity	≤ 3.0 µm
Cladding Non-Circularity	< 2.0%
Core Non-Circularity	≤ 5.0%
Coating Diameter	245 ± 5 µm
Coating-Cladding Concentricity	< 12 µm

### Environmental Specifications

Environmental Test	Test Condition	Induced Attenuation 850 nm and 1300 nm (dB/km)
Temperature Dependence	-60°C to +85°C	≤ 0.20
Temperature Humidity Cycling	-10°C to +85°C and 4% to 98% RH	≤ 0.20
Operating Temperature Range	-60°C to +85°C	

### Mechanical Specifications

Proof Test	The entire fiber length is subjected to a tensile stress $\geq 100$ kpsi (0.7 GN/m <sup>2</sup> ).
Length	Fiber lengths available up to 17.6 km/spool.

### Performance Characterizations

Refractive Index Difference	2%
Effective Group Index of Refraction	850 nm: 1.496 1300 nm: 1.491
Fatigue Resistance Parameter (nd)	20
Coating Strip Force	Dry: 0.6 lbs (2.7N) Wet: 14 days in 23°C water soak: 0.6 lbs (2.7N)
Chromatic Dispersion	Zero Dispersion Wavelength ( $\lambda_0$ ): 1332 nm $\leq \lambda_0 \leq$ 1354 nm Zero Dispersion Slope (S0): $\leq 0.097$ ps/(nm <sup>2</sup> *km)

Art.-No.	Description
TML-M06SCADK/MPP09E	tML® - FO Module MPO/MTP® with Pins/6x SC APC Duplex 9/125µ OS2
TML-M06SCDK/MPP09E	tML® - FO Module MPO/MTP® with Pins/6x SC Duplex 9/125µ OS2
TML-M06SCDK/MPP50G	tML® - FO Module MPO/MTP® with Pins/6x SC Duplex 50/125µ OM2
TML-M06SCDK/MPP50G3	tML® - FO Module MPO/MTP® with Pins/6x SC Duplex 50/125µ OM3
TML-M06SCDK/MPP50G4	tML® - FO Module MPO/MTP® with Pins/6x SC Duplex 50/125µ OM4
TML-M06SCDK/MPP62G	tML® - FO Module MPO/MTP® with Pins/6x SC Duplex 62,5/125µ OM1