

## Description

tML® is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site – especially in data centres, but also in industrial environments – within the shortest possible time. Heart of the system are the rear MPO/MTP® and Telco connectors, which can be used to connect at least six or twelve ports at a time. Depending on the module configuration, transfer rates of up to 400G are currently possible with SR4. The fibre optic and TP modules can be used together in a module carrier with a very high port density. The tde offers its tML® cabling system as a proven tML® standard system and in the highly innovative variants tML® 12, tML® 24, tML® 32 and now tML® 24+ System for extreme scalability and very easy migration to higher transmission rates such as 40G, 100G, 200G, 400G and 800G and more.

The tML® - FO Module MPO/MTP® is intended for the installation in the tML® Rack Mount Enclosure 1U (for 8 x Modules).

## Technical Data

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP® plug has a defined fiber height of 1 - 3.5µ. The max. adjacent fiber height difference is 0.2µm and for all fibers 0.3µm. All system components (modules, trunk cables and patch cords) are co-ordinated for the reaching of the performance particularly. The module is marked with sequential serial number and article number. The modules are ROHS compliant.

Box	Galvanized steel sheet
Front Panel	Stainless steel
Entry	2 x MPO/MTP® Male Adapter (black) back
Exit	3 x URM K8/K8 Adapter (metal) front
Tests	Interferometer, Insertion Loss, Return Loss and Visual Final Inspection; all measured values are electronically archived
	QS-Managementsystem ISO 9001, ISO 14001 and TL 9000

### Optical Performance

Fiber	Type	Wavelength	IL typ.	IL max.	RL min.
50/125µ OM2	MPO/MTP®	850 nm	≤ 0.35 dB	0.45 dB	20 dB
50/125µ OM2	URM K8/K8	850 nm	≤ 0.20 dB	0.29 dB	35 dB
50/125µ OM2	Module	850 nm	≤ 0.48 dB	0.70 dB	20 dB

Box	Galvanized steel sheet
Front Panel	Stainless steel
Dimensions	110 x 108 x 20 mm

Type	Corning 50/125µ OM2 multimode fiber
Manufacturer	Corning

#### Optical Specifications

Bandwidth	500 at 850 nm / 500 at 1300 nm
Attenuation	At 850 nm max. ≤ 2.5 dB/km At 1300 nm max. ≤ 0.8 dB/km
Numerical Aperture	0.200 ± 0.015

#### Dimensional Specifications

Core Diameter	50.0 ± 3.0 µm
Cladding Diameter	125.0 ± 2.0 µm
Core-Clad Concentricity	≤ 3.0 µm
Cladding Non-Circularity	< 2.0%
Core Non-Circularity	≤ 5.0%
Coating Diameter	245 ± 5 µm
Coating-Cladding Concentricity	< 12 µm

#### Environmental Specifications

Environmental Test	Test Condition	Induced Attenuation 850 nm and 1300 nm (dB/km)
Temperature Dependence	-60°C to +85°C	≤ 0.20
Temperature Humidity Cycling	-10°C to +85°C and 4% to 98% RH	≤ 0.20
Operating Temperature Range	-60°C to +85°C	

#### Mechanical Specifications

Proof Test	The entire fiber length is subjected to a tensile stress ≥ 100 kpsi (0.7 GN/m <sup>2</sup> ).
Length	Fiber lengths available up to 8.8 km/spool.

#### Performance Characterizations

Refractive Index Difference	2%
-----------------------------	----

Effective Group Index of Refraction	850 nm: 1.490 1300 nm: 1.486
Fatigue Resistance Parameter (nd)	20
Coating Strip Force	Dry: 0.6 lbs (2.7N) Wet: 14 days in 23°C water soak: 0.6 lbs (2.7N)
Chromatic Dispersion	Zero Dispersion Wavelength ( $\lambda_0$ ): 1300 nm $\leq \lambda_0 \leq$ 1320 nm Zero Dispersion Slope (S0): $\leq 0.101$ ps/(nm <sup>2</sup> *km)

Type	MPO/MTP®
Application	Multimode OM1/OM2
Design	without Flange
Connector style	SC Simplex
Key Orientation	Type A, Key up/down
Color	Beige
Material	Plastic
Sleeve	--
Shutter	--
Standards	IEC 61754-7 TIA 604-5
Manufacturer	US Conec

Type	URM
Case	plastic, blue
	core blue– singlemode
	core green – singlemode APC
sleeves	Ceramic slotted
Mating cycles	$\geq 1.000$
Operating temperature	-40°C to +85°
Flap	--
Manufacturer	tde
Possible fiber types	MM G50/65,2 / 125µm OM1 – OM5 & SM E9 / 125µm OS2

Connector Type	URM
----------------	-----

# tML® - FO Module 2x MPO/MTP® with Pins/3x URM K8/K8 50/125µ OM2

## Optical performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125µ OM2	URM	850 nm	≤ 0.20 dB	0.29 dB	35 dB
62.5/125µ OM1	URM	850 nm	≤ 0.20 dB	0.29 dB	35 dB

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP® plug has a defined fiber height of 1 - 3.5µ. The max. adjacent fiber height difference is 0.2µm and for all fibers 0.3µm.

Type	MPO/MTP® Male Push Pull Locking with Elite Pins (beige)
Ferrule	12 Fiber MM Elite® ferrule, PPS
Boot colour	Black
Temperature range	-40°C to +75°C
Manufacturer	tde/US Conec

## Optical Performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125µ OM2	MPO/MTP®	850 nm	≤ 0.25 dB	0.45 dB	20 dB
62.5/125µ OM1	MPO/MTP®	850 nm	≤ 0.25 dB	0.45 dB	

Art.-No.	Description
TML-M03URM8A/MPP09E	tML® - FO Module 2x MPO/MTP® with Pins/3x URM K8/K8 APC 9/125µ OS2
TML-M03URM8/MPP09E	tML® - FO Module 2x MPO/MTP® with Pins/3x URM K8/K8 9/125µ OS2
TML-M03URM8/MPP50G	tML® - FO Module 2x MPO/MTP® with Pins/3x URM K8/K8 50/125µ OM2
TML-M03URM8/MPP50G3	tML® - FO Module 2x MPO/MTP® with Pins/3x URM K8/K8 50/125µ OM3
TML-M03URM8/MPP50G4	tML® - FO Module 2x MPO/MTP® with Pins/3x URM K8/K8 50/125µ OM4
TML-M03URM8/MPP62G	tML® - FO Module 2x MPO/MTP® with Pins/3x URM K8/K8 62,5/125µ OM1